

PRODUCT SPECIFICATION

Handsfree Motion Sensor Headlamp Model: CH34

Revision History

Revision	Date	Initiator	Reason for Change
1.0	4 th Jan 2019		First Release

Prepared By	Approved By	
Wallace Tso	Wallace Tso	
Date: 4 th Jan 2019	Date: 4 th Jan 2019	

GPI International Limited


7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com Website: http://www.gpbatteries.com

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

GP Batteries

Product Specifications

Model no.: CH34



Product Name	:	Handsfree Motion Sensor Headlamp
Lumen output*		Cool white LED: 160lm / 48lm (+/- 15%)
		Red LED: 0.7lm (+/- 15%)
Beam Distance*	:	Max 90m (+/- 15%)
Runtime	:	Cool white LED: 160lm: 3 hours / 48lm: 20 hours
		Red LED: 44 hours
Battery type	:	3 x AAA
LED chip	:	CREE LED
IP rate*	:	IPX4
Shock proof*	:	Impact resistant, 1m
Dimensions	:	60 x 45 x 35 mm
Weight	:	56.9 g (without batteries), 93 g (with batteries)
Accessories Included	:	3 x AAA Batteries
Certification	:	CE, ROHS

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.