



GENERAL PRODUCT SPECIFICATION

Item No.	MRO30-P-E
-----------------	------------------

Date	16-6-2017	Replaces	4-11-11	No. Pages	1
-------------	-----------	-----------------	---------	------------------	---

Product Description:

Style	Blanket Roll; high strength perforation every 76 cm for single or multiple/variable length pads
Item Size (each)	76 cm wide by 46 m long
Color	Gray
Composition	Polypropylene >98%, Surfactant < 1.0%, color pigment < 1.0 %
Structure	96% natural white meltblown nonwoven fibers(<10 microns) 4% white spunbond nonwoven coverstock(<15-30 microns)
Technology	Meltblown + spunbond
Absorbency	Universal (Hydrophilic + Oleophilic)
Bonding	Bonded (staggered pattern) + Mechanical entanglement

Intended Application	Low -Lint Chemical Resistant Sorbent for Water, Oil, or Solvent Base Liquids
-----------------------------	--

Absorbency Capacity	185 l per bale (saturated; medium viscosity-12.5x)
----------------------------	--

Packaging Description:

Package configuration	Case	Pkg. Weight	14 kg (12.8 kg)
Items per Package	1 Bale / Case	Pkg. Dimensions	46cm x 46cm x 79cm (H)
Container type	Carton		

Physical Properties:

<u>Parameter</u>	<u>SPC Test Method</u>	<u>Units</u>	<u>Nominal</u>	<u>(+/-)Tolerance</u>
Basis Weight	SPCTM-002A	G/M2	365	36
Caliper	SPCTM-020	mm	5.2	0.5
Absorbency ** (med. Oil)	SPCTM-004B	gL/gS	12.5	2
Tensile Strength	SPCTM-007	daN	20	2
Color	Visual	-----	Gray	per standard

The above properties are “nominal” values used for PROCESS CONTROL when the product is produced and/or inspected. Performance “nominals” may vary depending upon the specific application, and/or the environment being applied, stored, or shipped.

**** The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.**

Attributes	Product will be free of foreign material contamination, rips, holes, and tears.
Labeling	Each package to be clearly labeled with Company Name, Address, Item No., Date, and/or Package Code (Bar Code).
Certification	Make no changes in basic process or composition without notifying customer. Claims for non-conformance of goods must be made within 60-days of delivery.