



GELIA CABLE REEL 25M GROUND 3G1.5 HO7RN-F THERMAL FUSE ARTICLE NO: 01.0009425 BARCODE: 7318270094258 Wire area: 1.5 mm² Rubber Cable H07RN-F

Degree of protection (IP): IP44

Number of sockets grounded: 4

Cable length: 25 m

Max load capacity: 1000-3000 W

With protective conductor: Yes

Rated current: 16 A

Rated voltage: 230 V

The cable reel is equipped with a thermal fuse that breaks the current in case of overheating. Durable and flexible, weather and oil resistant rubber cable (H07RN-F). Approved for outdoor use.

The cable reel's maximum load stated on the article refers to fully coiled or fully uncoiled cable. Outlets: Four "schuko" 230V 16A