

Accessories: Sensors



Temp., Humidity, Air pressure Sensor
7104, 7105, 7106 (RJ45 plug)



new

Calibrated Temp., Humidity, Air pressure Sensor
7104-2, 7105-2, 7106-2 (RJ45 plug)



Temperature Sensor 7201 (RJ45 socket)
Temp., Humidity Sensor 7202



Smoke Detector 7311, 7312



Leakage Point Sensor 7313

| Order Code | Product | Feature | Compatible to |
|------------|---|---|---|
| 7104 | Temperature Sensor 7104 | Cable sensor, RJ45 connector, -20°C to +80°C, cable length ca. 2.3 m | Expert Power Control 1104, 1105, 8021, 8031, 8041, 8221, 8226, 8314, 8316 Expert PDU Energy 8311, 8341 Expert Transfer Switch 8801 Expert Net Control 2111, 2191, 2302 Expert Sensor Box 7213, 7214 |
| 7105 | Temp., Humidity Sensor 7105 | Cable sensor, RJ45 connector, -20°C to +80°C, 0-90% humidity, cable length ca. 2.3 m | as for 7104 |
| 7106 | Temp., Humidity, Air pressure Sensor 7106 | Cable sensor, RJ45 connector, 20°C to +80°C, 0-90% humidity, 300-1100 hPa, cable length ca. 2.3 m | as for 7104 |
| 7104-2 | Temperature Sensor 7104-2 | Cable sensor with calibrated temperature range , RJ45 connector, -20°C to +80°C, cable length ca. 2.3 m | as for 7104 |
| 7105-2 | Temp., Humidity Sensor 7105-2 | Cable sensor with calibrated temperature range , RJ45 connector, -20°C to +80°C, 0-90% humidity, cable length ca. 2.3 m | as for 7104 |
| 7106-2 | Temp., Humidity, Air pressure Sensor 7106-2 | Cable sensor with calibrated temperature range , RJ45 connector, 20°C to +80°C, 0-90% humidity, 300-1100 hPa, cable length ca. 2.3 m | as for 7104 |
| 7201 | Temperature Sensor 7201 | Box case with RJ45 socket, -20°C to +80°C | as for 7104 |
| 7202 | Temp., Humidity Sensor 7202 | Box case with RJ45 socket, -20°C to +80°C, 0-90% humidity | as for 7104 |
| 7311 | Optical Smoke Detector 7311 | Overhead installation (d=100 mm), screw terminal NO or NC | Expert Net Control 2111, 2191, 2302 Expert Sensor Box 7214 |
| 7312 | Thermal Smoke Detector 7312 | Overhead installation (d=100 mm), screw terminal NO or NC | as for 7311 |
| 7313 | Leakage Point Sensor 7313 | 13 mm two-tined, detects flooding, operation by 12 V, 4-core cable (2.5 m) | as for 7311 |