KERN HCN 200K500IP



Robust, compact hanging scale with high level of protection against dust and water spray



Category	
Brand	KERN
Product category	Industrial scales
Product group	Hanging balances

Measuring System	
Readability [d]	500 g
Weighing capacity [Max]	200 kg
Eccentric/Off-centre loading is not possible	1
Tolerance (% of [Max])	0,5%
Reproducibility	0,5 kg
Linearity	± 1 kg
Weighing system	Strain gauge
Resolution	400
Units	kg lb N
Default unit	kg
Stabilization time	2 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	100 kg (M3)
Internal measuring frequency	5 Hz

Approval	
CE mark	✓
Display	
Display digit height	12 mm

Construction	
Dimension housing (W×D×H)	96×48×179 mm

Material housing	stainless steel
Material load hook	stainless steel

Functions	
Number of keys for operation	3
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Hold function	✓
Underfloor weighing	None
IP protection - complete device	IP65

Power Supplay	
Supplied plug-in power supply	Battery
Battery	2×1.5 V AA
Battery operating time	200 h

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	150×220×73 mm
Net weight approx.	0,50 kg
Gross weight approx.	1,2 kg

961-249
963-129H
969-517

Piktogramme

STANDARD















OPTION

