



# Heat Shrink Tubing

## HDT-A Thick Wall Adhesive Coated Tubing

### Data Sheet

#### Product Description

HDT-A is a thick wall polyolefin tubing. The toughness and weatherability of the tubing make it well suited for exposed applications. HDT-A is supplied with a specially designed hot melt adhesive layer. The adhesive is applied during extrusion of the tubing thus achieving a very smooth, constant adhesive layer, which ensures excellent sealing properties. HDT-A meets the longitudinal sealing requirements of VDE 0278 part 3 and is, therefore, ideal for sealing underground or exposed inline joints and terminations.

#### Technical Features

Continuous operating temperature range:	-55°C to +130°C Outer wall only	Shrink ratio:	Up to 4 : 1
Base material:	Polyolefin	Shrink temperature:	135°C (min)
Flammability	Self extinguishing Outer wall only	Longitudinal change:	-10% max
Tensile strength:	20 N/mm <sup>2</sup> total wall	Dielectrical strength	110 kV/cm
Specifications:	Germanischer Lloyd Type S Vureau Veritas 2557/4889	VDE 0278 part 3 Lloyds Register of Shipping	MIL-I-23053/15

Note: Det Norske Veritas version available (MDT-A-F471)

#### Ordering Information Type HDT-A

Bore as supplied minimum (mm)	Bore recovered maximum (mm)	Wall thickness fully recovered total wall (mm)	Wall thickness fully recovered meltable wall (mm)	Standard pack 1.0M length (M)	Standard Colour
12.0	3.0	3.2	0.7	100	Black
19.0	6.0	3.3	0.8	100	
30.0	8.0	4.8	0.8	40	
38.0	12.0	4.8	0.8	30	
48.0	15.0	4.8	0.8	15	
85.0	26.0	4.8	0.8	8	
115.0	38.0	4.8	0.8	5	

#### Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law. 3M is a trademark of the 3M Company. Printed in the UK. © 3M United Kingdom PLC, 2003.

**3M UK PLC**  
**Electrical Products**  
 3M Centre, Cain Road  
 Bracknell, Berkshire RG12 8HT  
 Telephone: 01344 858616  
 Fax: 01344 858758

**3M Ireland**  
**Sales Office**  
 3M House, Adelphi Centre  
 Dun Laoghaire, Co Dublin, Ireland  
 Telephone: 353 1 280 3555  
 Fax: 353 1 280 3509

**3M UK PLC**  
**Sales Office**  
 PO Box 393  
 Bedford MK41 0YE  
 Telephone: 01234 229462  
 Fax: 01234 229433