

## Brother HL-1110 laser printer 2400 x 600 DPI A4

**Brand :** Brother

**Product code:** HL-1110

**Product name :** HL-1110



HL-1110 - 20 ppm, 2400 x 600 dpi, 200 MHz, 1MB, USB 2.0, GDI, 380W, 51dB, 4.5 Kg

### Brother HL-1110 laser printer 2400 x 600 DPI A4:

This easy to use single function printer combines affordability with a compact footprint and proven reliability you would expect from the number one brand in the mono laser market.

Which means users can trust in its performance, thanks to 20ppm print speed, up to 600x600dpi resolution and full speed USB 2.0 interface making it an ideal device for home and small offices.

- Help increase productivity with print speeds up to 20ppm
- Small, space saving design
- 150 sheet paper capacity
- Full speed USB 2.0 Interface
- Print professional documents with output up to 600 x 600 dpi (2400 x 600 dpi with Resolution Control)
- Easy replacement 1,000 page toner cartridges.

Brother HL-1110. Print technology: Laser. Number of print cartridges: 1. Maximum resolution: 2400 x 600 DPI. Maximum ISO A-series paper size: A4. Print speed (black, normal quality, A4/US Letter): 20 ppm. Product colour: Black, White

Printing		Performance	
Colour *	✗	Processor frequency	200 MHz
Print technology *	Laser	Sound pressure level (printing) *	51 dB
Duplex printing *	✗	Design	
Maximum resolution *	2400 x 600 DPI	Product colour *	Black, White
Print speed (black, normal quality, A4/US Letter) *	20 ppm	Power	
Features		Power consumption (printing) *	380 W
Recommended duty cycle	250 - 1800 pages per month	Power consumption (standby)	40 W
Number of print cartridges *	1	Power consumption (PowerSave)	0,5 W
Page description languages *	GDI	Power consumption (off)	0,28 W
Input & output capacity		System requirements	
Total input capacity *	150 sheets	Windows operating systems supported Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64 Mac operating systems supported Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion Linux operating systems supported ✓	
Total output capacity *	50 sheets		
Paper handling			
Maximum ISO A-series paper size *	A4		
Maximum print size	210 x 297 mm		
Paper tray media types *	Plain paper, Recycled paper		
ISO A-series sizes (A0...A9) *	A4		
Non-ISO print media sizes	Folio, Letter		
Paper tray media weight	65 - 105 g/m <sup>2</sup>		
Ports & interfaces			
Standard interfaces	USB 1.1, USB 2.0		
USB 2.0 ports quantity	1		
Network			
Network ready *	✗		
Wi-Fi *	✗		
Ethernet LAN *	✗		
Performance			
Internal memory *	1 MB		

**System requirements**

Server operating systems supported Windows Server 2003, Windows Server 2003 R2, Windows Server 2008, Windows Server 2008 R2

**Weight & dimensions**

Width	340 mm
Depth	238 mm
Height	189 mm
Weight	4,5 kg

**Packaging data**

Package width	415 mm
Package depth	313 mm
Package height	294 mm
Package weight	5,3 kg



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.