HMIDT542

10.4 Touch Smart Display SVGA





Main

Range of product	Harmony GTU
Product or component type	Flat screen
Terminal type	Touchscreen display
[Us] rated supply voltage	1224 V DC power supply
Supply voltage limits	10.828.8 V
Power consumption in W	15 W
Inrush current	30 A

Complementary

Integrated connection type	USB 2.0 type A	
integrated comments, po	USB 2.0 type mini B	
Touchscreen resolution	1024 x 1024	
Pixel resolution	800 x 600	
Display size	10.4 inch	
Aspect ratio	4:3	
Display type	Colour TFT LCD	
Display resolution	800 x 600 pixels SVGA	
Display colour	16 million colours	
Backlight lifespan	50000 hours	
Touch panel	Multi touch analogue resistive	
Function available	Brightness sensor	
Type of cooling	Natural convection	
Type of installation	Indoor installation	
Cut-out dimensions	259 (+ 1/- 0) x 201 (+ 1/- 0) mm	
Width	272.5 mm	
Height	214.5 mm	
Depth	67 mm	
Net weight	2.7 kg	

Environment

IP degree of protection	Front panel: IP66	
	Front panel: IP67	
NEMA degree of protection	NEMA 4X front panel	
Standards	UL 508	
	ANSI/ISA 12-12-01	
	Class I division 2 CSA C22.2 No 213	
	CSA C22.2 No 142	
	IEC 61132-2	
Product certifications	CULus	
	CE	
	KC	
	RCM	
Ambient air temperature for operation	060 °C conforming to EN 61131-2	
Ambient air temperature for storage	-2060 °C	
Relative humidity	1090 % non-condensing	
Operating altitude	2000 m	

Vibration resistance 3.5 mm constant amplitude (f = 59 Hz) conforming to E 9.8 m/s ² (f = 9150 Hz) conforming to EN/IEC 61131-2		
Shock resistance	147 m/s² conforming to EN/IEC 61131-2	
Electromagnetic compatibility	tibility Electrostatic discharge immunity test level 3 conforming to EN/IEC 6100	
Packing Units		
Unit Type of Package 1	pe of Package 1 PCE	
. ,,,		

3.826 kg

210.0 mm

330.0 mm

370.0 mm

Offer Sustainability	Offer	Sustai	nability
----------------------	-------	--------	----------

Package 1 Weight

Package 1 Height

Package 1 width

Package 1 Length

Sustainable offer status	Green Premium product	
REACh Regulation	☑ REACh Declaration	
REACh free of SVHC	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	☑ China RoHS Declaration	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	


Contractual warranty

Warranty	18 moi	nths

HMIDT542


External Dimensions

Display Unit with Box Module



- 1 Front
- 2 Left
- 3 Bottom

Installation with Installation Fasteners and Dimensions with Cables




- (A) Rotation area of the fastener
- (B) Pitch of the center of installation fastner screws
- 1 Right
- 2 Front
- 3 Left
- 4 Bottom

Product data sheet Mounting and Clearance

HMIDT542

Mounting

Panel Cut Dimensions



Dimensions in mm


A	В	С	R
259 (+1/-0)	201 (+1/-0)	1.65	3 max.

Dimensions in in.

A	В	С	R
10.2 (+0.04/-0)	7.91 (+0.04/-0)	0.060.2	0.12 max.

Installation Requirements

Mounting Angle



When installing this product in a slanted position with an incline more than 30°, the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan, A/C) to ensure the ambient operating temperature is 40 °C or less (104 °F or less).

Clearance



