Product data sheet Characteristics

HMIDT551

10W Touch Advanced Display WXGA





Main

Range of product	Harmony GTU	
Product or component type	Advanced touchscreen panel	
Terminal type	Touchscreen display	
[Us] rated supply voltage	1224 V DC power supply	
Supply voltage limits	10.828.8 V	
Power consumption in W	6.5 W	
Inrush current	30 A	

Complementary

o o mpromornary			
Touchscreen resolution	1024 x 1024		
Pixel resolution	1280 x 800		
Display size	10.1 inch		
Aspect ratio	4:3		
Display type	Colour TFT LCD		
Display resolution	1280 x 800 pixels WVGA		
Display colour	262144 colors		
Backlight lifespan	50000 hours		
Touch panel	Single touch analogue resistive		
Type of cooling	Natural convection		
Type of installation	Indoor installation		
Cut-out dimensions	255 (+ 1/- 0) x 185 (+ 1/- 0) mm		
Width	268.5 mm		
Height	198.5 mm		
Depth	67 mm		
Net weight	2.5 kg		

Environment

IP degree of protection	Front panel: IP66	
	Front panel: IP67	
NEMA degree of protection	NEMA 4X front panel	
Standards	UL 508 ANSI/ISA 12-12-01 Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 IEC 61132-2	
Product certifications	RCM CULus KC CE	
Ambient air temperature for operation	060 °C conforming to EN 61131-2	
Ambient air temperature for storage	-2060 °C	
Relative humidity	1090 % non-condensing	
Operating altitude	2000 m	
Vibration resistance	3.5 mm constant amplitude (f = 59 Hz) conforming to EN/IEC 61131-2 9.8 m/s ² (f = 9150 Hz) conforming to EN/IEC 61131-2	

Shock resistance	147 m/s² conforming to EN/IEC 61131-2		
Electromagnetic compatibility	Electrostatic discharge immunity test level 3 conforming to EN/IEC 61000-4-2		
Packing Units			
Unit Type of Package 1	PCE		
Number of Units in Package 1	1		
Package 1 Weight	3.853 kg		
Package 1 Height	21.0 cm		
Package 1 width	33.0 cm		
Package 1 Length	37.0 cm		
Unit Type of Package 2	P12		
Number of Units in Package 2	10		
Package 2 Weight	96.69 kg		
Package 2 Height	80.0 cm		
Package 2 width	120.0 cm		
Package 2 Length	110.0 cm		
Unit Type of Package 3	CAR		
Number of Units in Package 3	2		
Package 3 Weight	8.769 kg		
Package 3 Height	43.0 cm		
Package 3 width	35.5 cm		
Package 3 Length	45.5 cm		
Offer Sustainability			
Sustainable offer status	Green Premium product		
REACh Regulation	REACh Declaration		
REACh free of SVHC	Yes		
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Mercury free	Yes		
RoHS exemption information	₽¥Yes		
China RoHS Regulation	Ğ China RoHS Declaration		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	☑ End Of Life Information		
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		


18 months

Warranty

HMIDT551


External Dimensions

Display Unit with Box Module



- 1 Front
- 2 Left
- 3 Bottom

Installation with Installation Fasteners and Dimensions with Cables




- (A) Rotation area of the fastener
- (B) Pitch of the center of installation fastner screws
- 1 Right
- 2 Front
- 3 Left
- 4 Bottom
- 5 Top

Product data sheet Mounting and Clearance

HMIDT551

Mounting

Panel Cut Dimensions



Dimensions in mm


A	В	С	R
255 (+1/-0)	185 (+1/-0)	1.65	3 max.

Dimensions in in.

Α	В	С	R
10.04 (+0.04/-0)	7.28 (+0.04/-0)	0.060.2	0.12 max.

Installation Requirements

Mounting Angle



When installing this product in a slanted position with an incline more than 30°, the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan, A/C) to ensure the ambient operating temperature is 40 °C or less (104 °F or less).

Clearance



