

HNS L 24 W 2G11

PURITEC HNS UV-C | UV-C lamps for purification



Areas of application

- Efficient disinfecting of air, water and surfaces

Product family benefits

- Effective and environment-friendly disinfection without chemicals
- Low mercury content
- Long lifetime due to specific coating
- Ozone-free

Product family features

- Dominant wavelength: 254 nm (OFR version)



Product datasheet

Technical data

Product information

Order reference	HNS-L 24W 2G11
-----------------	----------------


Electrical data

Nominal voltage	87.0 V
Lamp voltage	87 V
Construction voltage	87.00 V
Nominal current	0.35 A
Lamp current	0.35 A
Nominal wattage	24.00 W

Photometrical data

Luminous intensity	7800 cd
Radiated power 200...280 nm (UVC)	7.3 W

Dimensions & weight



Diameter	40.0 mm
Length	314.5 mm

Lifespan

Lifespan	9000 h
----------	--------

Additional product data

Base (standard designation)	2G11
-----------------------------	------

Capabilities

Burning position	s180
------------------	------

Product datasheet

Country specific categorizations

Order reference	HNS-L 24W 2G11
------------------------	----------------

Country specific information

Product code	METEL-Code	SEG-No.	STK number	UK Org
4008321220561	-	-	4834807	-
4008321220561	-	-	4834807	-

HNS L 24 W 2G11

PURITEC HNS UV-C | UV-C lamps for purification

Product name	Product name ECG	EAN
HNS L 24 W 2G11	QT-ECO 1x18-24/220-240 S	4050300638560
	QTP-OPTIMAL 1x18-40	4008321873743
	QTP-OPTIMAL 2x18-40	4008321873767

Product datasheet

Safety advice

PURITEC germicidal lamps emit high-intensity UV radiation that can cause sunburn and conjunctivitis. The skin and eyes must therefore not be exposed to direct or reflected unfiltered radiation.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321220561	HNS L 24 W 2G11	Folding carton box 1	49 mm x 27 mm x 347 mm	0.46 dm ³	110.00 g
4008321220578	HNS L 24 W 2G11	Shipping carton box 10	288 mm x 190 mm x 136 mm	7.44 dm ³	1202.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
