HP ScanJet Pro 3000 s4

(6FW07A)



Fast, affordable, and designed to handle everything from simple colour jobs to complex workflows. Quickly and reliably digitise larger projects with scan speeds up to 40 ppm/80 ipm and a 50 page ADF.¹ Recommended for 4,000 pages per day.





Small size. Fast scans. Same reliable results.

- Produce scans at up to 40 ppm/80 ipm¹ with two-sided scanning that captures both sides at once.
- Free up space for work. This HP ScanJet Pro is small and slim a modern design perfect for the desktop.
- Don't wait for warm-up HP Instant-on Scanning lets you begin scanning quickly.
- Load up to 50 pages into the automatic document feeder for fast, unattended scanning.

Optimise workflows with one-touch scanning

- Streamline routine work with one-touch scanning create one-button, custom settings for recurring scan jobs.
- Scan images directly into applications with included and full-featured TWAIN and ISIS®.
- Easily transfer scans into editable text, searchable PDF files, and more file types, using built-in OCR.
- Quickly share or archive scans directly to popular cloud destinations with HP Scan software.

Capture business documents like a pro

- Define scan profiles for common document types, and scan to multiple destinations with HP Scan software.
- Capture and organise documents, business cards, and other file types with feature-rich software.
- Produce clear, legible scans up to 1,200 dpi resolution.

Accessories and services

Accessories	7QH79A HP ScanJet 2000s2/3000s4/4000snw1 Roller Replacement Kit 8PA50A HP 5-pack Carrier Sheet Kit C9943B HP ADF Cleaning Cloth Package
Service and Support	U9JQ2E HP 3 year Standard Exchange for ScanJet Pro 3000 service U9JQ3E HP 3 year Next Business Day Exchange for ScanJet Pro 3000 service U9JQ4E HP 3 year Next Business Day Onsite Exchange for ScanJet Pro 3000 service U9JQ5E HP 3 year Return to Depot for ScanJet Pro 3000 service U9JQ6FE HP 1 year Post Warranty Standard Exchange for ScanJet Pro 3000 service U9JQ7PE HP 1 year Post Warranty Next Business Day Exchange for ScanJet Pro 3000 service U9JQ8PE HP 1 year Post Warranty Next Business Day Onsite Exchange for ScanJet Pro 3000 service U9JQ9PE HP 1 year Post Warranty Return to Depot for ScanJet Pro 3000 service U9JT1E HP Installation Service wireless/network Personal Scanner & Printer

Technical specifications

Control panel	Scan button, Power button with a LED and a LED for Error indication
Scanner specifications	Scanner type Sheetfed; Scan technology: CMOS CIS (Contact Image Sensor); Scan input modes: One default scan mode on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA; Twain version: Windows: 32-bit and 64-bit TWAIN version 2.1; Mac: n/a; Colour scanning: Yes; Output resolution dpi settings: 75; 150; 200; 240; 300; 400; 500; 600; 1200 ppi;
Scan speed ³	Up to 40 ppm/80 ipm
Scan resolution	Optical Up to 600 dpi; Hardware: 600 x 600 dpi
Scan file format	For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.txt) and Searchable PDF
Scanner advanced features	Auto exposure; Auto threshold; Auto detect colour; Background smooth/removal; Auto detect size; Straighten content; Enhance content; Multi-streaming; Auto feed; Multi-feed detection sensor; Advanced multi-feed detection; Auto orient; Multi-colour dropout; Channel colour dropout; Edge erase; Delete blank page; Merge pages; Hole fill; PDF permissions; Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR)
Grayscale levels/Bit depth	256/24-bit (external), 48-bit (internal)
Duty cycle	Recommended daily duty cycle: 4000 pages
Auto document feeder capacity	Standard, 50 sheets
Connectivity	Standard USB 3.0;
Memory	Standard 256 MB;
Media handling	
Media types	Cut Sheet Paper; Printed Paper (Laser and ink); Pre-Punched Paper; Bank Checks; Business Cards; Freight Bills; Carbonless forms; Plastic Carrier sheets for easily damaged documents; Previously stapled media with staple removed; Plastic cards (up to 1.24 mm thickness)
Media size (ADF)	ISO A4: 210 x 297 mm (8.3 x 11.7 in); JIS B5: 182 x 257 mm (7.2 x 10.1 in); ISO B5: 176 x 250 mm (7.0 x 9.9 in); ISO A5: 148 x 210 mm (5.8 x 8.3 in); ISO A6: 105 x 148 mm (5.8 x 4.1 in); ISO A7: 74 x 104 mm (2.9 x 4.1 in); ISO A8: 52 x 74 mm (2.0 x 2.9 in); Custom: 5.08 x 7.36 cm to 21.6 x 309.9 cm (2.0 x 2.9 in to 8.5 x 122 in)
Media weight (ADF)	40 to 210 g/m²
Compatible operating systems	Microsoft® Windows® (10, 8.1, 7, XP: 32/64 bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro); Citrix ready
Minimum system requirements	PC: macOS Catalina 10.15, macOS Mojave 10.14, macOS High Sierra 10.13, Microsoft® Windows® 10, 8.1, 7, XP: 32/64-bit, 2008 R2, 2012 R2, 2016, 2019, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Microsoft® Internet Explorer
Software included	Windows: HP WIA scan driver, HP TWAIN scan driver (32/64-bit), HP Scan, HP Scanner Tools Utility, I.R.I.S Readiris Pro, I.R.I.S Cardiris, OpenText ISIS
Print Server Specifications	
Security management	Power button to on/off device
Dimensions and weight	
Product dimensions (W x D x H)	Minimum : 300 x 172 x 154 mm; Maximum : 300 x 410 x 310 mm
Package dimensions (W x D x H)	397 x 248 x 242 mm
Product weight	2.7 kg
Package weight	4.2 kg
Operating environment	Temperature: 17.5 to 25°C Humidity: 30% to 70% relative humidity (RH)
Storage	Temperature: -40 to 60°C
Power ¹	Requirements: Input Voltage range: 220 - 240 VAC, Rated Frequency: 50 - 60HZ; Consumption: 4.4 Watts (ready), 24 Watts (scanning), 1.1 Watts (sleep), 0.1 Watts (auto-off), 0.1 Watts (off); ENERGY STAR: Yes
Certifications	IEC 60950-1:2005+A1:2009+A2:2013/EN 60950-1:2006+A11:2009+A1:2010+A12:2011+A2:2013; IEC 62479:2010/EN 62479:2010; IEC 62471:2006/EN62471:2008 Electromagnetic compatibility: CISPR 22:2008 & CISPR32:2012/EN 55032:2012 - Class B, EN 61000-3-2:2014, EN 61000-3-3:2013, EN 55024:2010 CECP; ENERGY STAR® 3.0 certified; EPEAT® Silver
What's in the box	6FW07A HP ScanJet Pro 3000 s4 Sheet-feed Scanner; Power cord; Power adapter; USB cable; Scanner engine; Flyers; Install guide
Warranty	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to http://www.hp.com/support to learn about HP world-class service and support options in your region.

Footnotes

1 Scan speed measured at 300 dpi (black-and-white, grayscale, and colour). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

Technical specifications disclaimers

- 1 Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device.

 ² EPEAT® registered where applicable. EPEAT registration varies by country. See http://www.epeat.net for registration status by country.

 ³ Sheet feed speeds: all resolutions up to and including 300 ppi; Simplex 40 A4 pages per minute; Duplex 80 A4 images per minute.

























