



HP 951XL High Yield Yellow Original Ink Cartridge (CN048AE)



Overview

HP 951XL Ink Cartridge, yellow

Count on professional-quality business documents that will impress customers. Page after page, documents and marketing materials will stand out with crisp blacks and brilliant color.

Reliable print performance for standout results

Original HP ink cartridges are reliable and print superb quality documents.

Professional color documents that impress

Black text and color graphics look sharp in your business documents with HP inks designed for the office.

Affordable, reliable everyday printing

Print impressive color business documents using Original HP inks.

Conveniently replace and recycle cartridges[5]

Easily return your print cartridges for recycling, using HP Planet Partners.[5]

Features



Designed to work the first time, every time^[8]



Quality prints you can take pride in



The environmental choice.^[9]



Better together. Better results.



Superb quality you can count on



Print your own marketing materials

[5] HP Planet Partners Program availability varies. For details, see <http://www.hp.com/recycle>. On recycled materials in cartridges, see <http://www.hp.com/go/recycledcontent>.

[8] See <http://www.hp.com/go/suppliesclaims>.

[9] HP Planet Partners Program availability varies. For details, see <http://www.hp.com/recycle>. On recycled materials in cartridges, see <http://www.hp.com/go/recycledcontent>.

Specifications

Ink types	Pigment-based
Color(s) of printing supplies	Yellow
Print Technology	Ink
Supply type	Cartridges
Ink drop	7 pl
Print head nozzles	1376
Print cartridge volume delivered	17 ml
Operating temperature range	5 to 35°C
Storage temperature range	-40 to 60°C
Operating humidity range	10 to 90% RH
Non-Operating Humidity Range	10 to 90% RH
Print Resolution Technologies	TIJ 4.x
Compatibility	HP Officejet Pro 8100 ePrinter series, HP Officejet Pro 8600 e-All-in-One series
Product count per unit	1
Case or master carton quantity	50
Quantity per pallet	4500
Count of carton in pallet	90
UPC number	(301) 886111615308; (303) 193015225633; (999) 886111755462; (ACU) 193015225640; (BGX) 886111748945; (BGY) 886111748990
Pallet barcode	(999) 20886111755466, (BGX) 20886111748949, (BGY) 20886111748994
Minimum dimensions (W x D x H)	114 x 126 x 25 mm
Minimum dimensions (W x D x H)	4.49 x 4.96 x 0.98 in
Package dimensions (W x D x H)	114 x 126 x 25 mm
Package dimensions (W x D x H)	4.49 x 4.96 x 0.98 in
Case or master carton dimensions (W x D x H)	383 x 249 x 156 mm
Case dimensions (case or master carton)	15.08 x 9.8 x 6.14 in
Pallet dimensions (W x D x H)	800 x 1200 x 1702 mm
Pallet dimensions	31.5 x 47.24 x 67.01 in
Case weight (case or master carton)	3.87 kg

Package weight	0.07 kg
Package weight	0.16 lb
Pallet weight	368 kg
Pallet weight	811.3 lb
Page Yield	1500
What's in the box	1 Cartridge
Manufacturer Warranty	HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty.

Additional specifications

Additional information about Eco	http://www.hp.com/go/ecosolutions
Cartridge Colors	Yellow
Case weight (case or master carton, imperial)	8.52 lb
Compatibility headline	HP 951 ink cartridges work with:
Count of cartons per pallet layer	9
Count of layers in pallet	10
Country of origin	Made in Singapore, Malaysia, China
Eco label	ENERGY STAR® qualified
Empty weight	27.41 g
Operating temperature range	41 to 95°F
Package count	1
Page yield (color)	~1,500 pages
Page yield (yellow)	1 Yellow (~1,500 pages)
Page yield footnote	Tested in HP Officejet Pro 8600 e-All-in-One. Approximate average based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details see http://www.hp.com/go/learnaboutsupplies
Photo (product photo, jpg, 190x170)	Ink Toner Paper Printer Supplies/hp-950-officejet-ink-cartridges_190x170.jpg
Photo (product photo, jpg, 70x100)	Ink Toner Paper Printer Supplies/hp-950-officejet-ink-cartridges_70x100.jpg
Print technology	HP Thermal Inkjet
Printhead swath (inch)	1.125 in
Product subgroup	High Capacity Ink Cartridges
Segment (filter)	OfficeJet Pro
Selectability	951XL
Smaller master carton barcode	(999) 10886111755469, (BGX) 10886111748942, (BGY) 10886111748997
Stacking number for pallet	2
Storage temperature range	-40 to 140°F
Subgroup	High Capacity Cartridges
UNSPSC code	44103105

Warranty

HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty. This warranty pertains to the product when used in its designated HP or authorized OEM printing device. HP will, at HP's option, either refund the purchase price or replace products that prove to be defective. Visit the HP online support web site <http://www.hp.com/support> for a list of support phone numbers and conditions or return to your point of purchase.

Weight

0.11 lb

Weight

0.05 kg

Disclaimer — Copyright

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 04, 2022 10:16 AM UTC+0000