



HP Chromebook 11MK G9 EE

Thin, durable Chromebook designed for students and learning

Help students reach their potential with cloud-first² learning on the rugged HP Chromebook 11MK G9 EE. At less than 19 mm (.748 in), this Chromebook keeps pace with active student lifestyles while the secure, fast-booting Chrome OS makes IT management easy.



Designed for reliability. Engineered for durability

- Say goodbye to downtime with a <19 mm (<.75 in) thin Chromebook that can withstand drops up to 122 cm (48.03 in)⁴ and undergoes MIL-STD 810H⁵ and HP education testing.³ The full-skirted anchored keyboard resists picking, minor spills, and dust.

Enable student productivity

- Get online quickly, stream lessons, complete assignments, and more with up to 8 GB RAM¹⁴ and Chrome OS. Stay productive with long battery life and fast recharging.⁷ Easily monitor, manage, and evaluate students with HP Classroom Manager.⁸

Learning happens everywhere

- Engage in lively virtual discussions and interactively collaborate with students and teachers on an HD webcam and optional HD IPS touchscreen.¹⁴ Powered by 2x2 802.11ac¹⁰, supporting MU-MIMO¹¹ and HP Extended Range Wireless LAN¹² for reliable connectivity even in crowded wireless networks.
- Breathe easy with the low-maintenance, highly manageable, and secured Chrome OS. With automatic software updates through June 2028 and built-in anti-virus protection, your device is protected and up to date.¹⁸
- Undergoes MIL-STD 810H and HP Total Test Process, featuring additional tests for HP education products, to ensure this Chromebook Education Edition exceeds HP durability and reliability standards—helping reduce total cost of ownership.^{3,5}
- Accidents happen. All the time. Give students a rugged Chromebook that can survive drops up to 76 cm (29.92 in) onto concrete and 122 cm (48.03 in) onto plywood. Drop tested for quality assurance and peace of mind.⁴
- Designed for busy students who are on the go, this octo-core MediaTek MT8183 processor combines convenient connectivity with low-power consumption so students can keep learning.⁶
- Reduce risk of damage to keyboards with pick resistant, full-skirted anchored keys. Coupled with an extra layer of protection under the keys, this sturdy keyboard resists dust and spills up to 350ml (11.8 oz).³
- Quickly get online and access materials, even in crowded wireless networks, with a 2x2 802.11ac Wi-Fi WLAN module supporting MU-MIMO and HP Extended Range Wireless LAN.^{10,11,12}
- Easily manage student activities and collaboration with the intuitive and interactive HP Classroom Manager. Monitor and evaluate students and provide supportive feedback in real-time—increasing engagement with dynamic learning materials.⁸
- Ready for the backpack, classroom, home, and beyond. At less than 19 mm (.748 in), the ultra-thin, durable design on this 11-inch diagonal Chromebook makes it easy for students to take their lessons with them.
- Tested for 1000 cleanings, the keyboard of this education edition Chromebook can be wiped down using commonly available household disinfecting and cleaning wipes.¹³

HP Chromebook 11MK G9 EE Specifications Table



Available Operating Systems	Chrome OS™
Processor family	MediaTek processor
Available Processors ^{1,2}	MediaTek MT8183 (2.0 GHz base frequency, 1 MB L2 cache, 8 cores)
Maximum memory	8 GB LPDDR4X-4266 SDRAM Memory soldered down.
Internal storage	32 GB up to 64 GB eMMC 5.0 ³
Display size (diagonal, metric)	29.5 cm (11.6")
Display	29.5 cm (11.6") diagonal, HD (1366 x 768), IPS, anti-glare, 220 nits, 50% NTSC; 29.5 cm (11.6") diagonal, HD (1366 x 768), touch, IPS, anti-glare, 220 nits, 50% NTSC; 29.5 cm (11.6") diagonal, HD (1366 x 768), SVA, anti-glare, 220 nits, 45% NTSC ^{6,7,8,18}
Available Graphics	Integrated: ARM® Mali™-G72 MP3 Graphics
Audio	HD audio, dual speakers, integrated microphone
Wireless technologies	(HP Extended Range Wireless LAN, MU-MIMO and Chromecast support)
Expansion slots	1 microSD (Supports SD, SDHC, SDXC.)
Ports and Connectors	2 USB 2.0 Type-C®; 1 USB 2.0 Type-A; 1 headphone/microphone combo
Input devices	Spill resistant, full-size, Chrome keyboard with skirt anchored keycaps; Touchpad with multi-touch gesture support, taps enabled as default;
Communications	Qualcomm® Atheros QCA6174A-5 802.11a/b/g/n/ac (2x2) Wi-Fi® and Bluetooth® 4.2 combo ;
Camera	720p HD camera ⁶
Software	Chrome Education Upgrade (Sold separately); HP Classroom Manager (Sold separately) ^{10,11}
Security management	Nano Security lock slot; Google Titan C ¹²
Fingerprint reader	Fingerprint reader not available
Power	HP Smart 45 W USB Type-C® adapter
Battery type	HP Long Life 2-cell, 47 Wh Li-ion polymer ^{13,17}
Dimensions	29.5 x 20.53 x 1.88 cm
Weight	Starting at 1.34 kg (Weight will vary by configuration.)
Energy efficiency compliance	ENERGY STAR® certified; EPEAT® 2019 registered where applicable. EPEAT® registration varies by country. See www.epeat.net for registration status by country. ¹⁵
Sustainable impact specifications	Low Halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable ^{16,21}
Warranty	1 year (1-1-0) limited warranty and service offering includes 1 year of parts and labor. Terms and conditions vary by country. Certain restrictions and exclusions apply.

HP Chromebook 11MK G9 EE

Accessories and services (not included)

HP Wireless Premium Mouse



Create a sleek, professional, clutter-free workspace and give yourself room to move around with the HP Wireless Premium Mouse, which integrates seamlessly with your HP notebook.
Product number: 1JR31AA

HP Reversible 11.6-inch Sleeve



Help protect your laptop¹ on the go with the ultralight HP Reversible 11.6 Sleeve that keeps it safe and lets you make a bold statement or be a little conservative—you decide.
Product number: 7ZE81AA

HP 3 year Next Business Day Onsite Hardware Support for Notebooks



Receive 3 years of next business day onsite HW support from an HP-qualified technician for your computing device, if the issue cannot be solved remotely.
Product number: UQ992E

HP Chromebook 11MK G9 EE

Messaging Footnotes

- ² Internet access required and not included.
- ³ HP Total Test Process testing is not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- ⁴ 122 cm test on plywood and 76 cm test on concrete. Drop test is not a guarantee of future performance under these test conditions. Any accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- ⁵ MIL-STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- ⁶ Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance will vary depending on your hardware and software configurations. MediaTek's numbering is not a measurement of clock speed.
- ⁷ Recharges the battery up to 90% within 90 minutes when the system is off or in standby mode, when used with the power adapter provided with the notebook, and no external devices are connected. After charging has reached 90% capacity, charging speed will return to normal. Charging time may vary +/-10% due to System tolerance.
- ⁸ HP Classroom Manager is sold separately. Control and device locking from the teacher's desktop requires purchase of HP Classroom Manager for Teachers.
- ¹⁰ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 5 (802.11 ac) is backwards compatible with prior 802.11 specs.
- ¹¹ Multiple-Input Multiple-Output (MU-MIMO) is a wireless technology that uses multiple transmitters and receivers to enhance data transfer. MIMO requires a MU-MIMO router, sold separately.
- ¹² Based on internal testing vs. previous generation product with 802.11ac wireless LAN module.
- ¹³ The keyboards of the HP Education portfolio, including the HP Chromebook 11MK G9 EE, have been tested to 1,000 wipes to be cleaned with Windex® Original Glass & Surface Wipes and Clorox® Disinfecting Wipes with EPA Registration Number 5813-79. Do not use wipes on other surfaces of the product. See user guide for cleaning instructions.
- ¹⁴ Optional feature that must be configured at purchase.
- ¹⁶ G Suite for Education is available to qualifying educational institutions from Google and requires internet access.
- ¹⁸ See <https://support.google.com/chrome/a/answer/6220366?hl=en> for more information.

Technical Specifications Footnotes

- ¹ Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. MediaTek's numbering, branding and/or naming is not a measurement of higher performance.
- ² Processor speed denotes maximum performance mode; processors will run at lower speeds in battery optimization mode.
- ³ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 30 GB (for Windows 10) is reserved for system recovery software.
- ⁴ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited.
- ⁵ Chromecast must be purchased separately.
- ⁶ HD content required to view HD images.
- ⁷ Resolutions are dependent upon monitor capability, and resolution and color depth settings.
- ⁸ HP Sure View integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.
- ⁹ Google Drive offer is tied to this device and is non-transferable. If this device is returned, the extra storage will be revoked. In order to redeem this offer, you will need to be on Chrome OS™ 23 or later. Internet access is required and not included. Additional information about storage plan refunds, renewals, cancellations and expiration is available at the Google website: <https://support.google.com/chromebook/answer/2703646?hl=en>
- ¹⁰ Chrome Education Upgrade requires one-time setup, subscription, Google Admin Console, and your organization's domain. Please see <https://support.google.com/a/answer/60216>.
- ¹¹ HP Classroom Manager is sold separately. Control and device locking from the teacher's desktop requires purchase of HP Classroom Manager.
- ¹² Lock is sold separately.
- ¹³ Recharges up to 90% within 90 minutes when the system is off or in standby mode when used with the power adapter provided with the notebook. After charging has reached 90% capacity, charging speed will return to normal. Charging time may vary +/-10% due to System tolerance.
- ¹⁴ HP Care Packs are sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
- ¹⁵ Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.
- ¹⁶ External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.
- ¹⁷ Actual battery Watt-hours (Wh) will vary from design capacity. Battery capacity will naturally decrease with shelf life, time, usage, environment, temperature, system configuration, loaded apps, features, power management settings and other factors.
- ¹⁸ Actual brightness will be lower with touch or HP Sure View.
- ¹⁹ Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 5 (802.11 ac) is backwards compatible with prior 802.11 specs.
- ²⁰ Multiple-Input Multiple-Output (MU-MIMO) is a wireless technology that uses multiple transmitters and receivers to enhance data transfer. MIMO requires a MU-MIMO router, sold separately.
- ²¹ 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.

Sign up for updates hp.com/go/getupdated

© Copyright 2021 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2020 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

March 2021

--

