



Power Converter 24 VDC - DC 12 V 10 A

General information

Switching converter for connecting 12V equipment to 24V battery. This fused converter has got output short circuit protection, overheating protection and overload protection. With E-mark approval, which is obliged since October 2002.

Specifications

Height:	45 mm
Width:	73 mm
Fuse:	Yes
Output current:	10 A
Input type:	Screw Terminal
Output voltage:	DC 12 V
Output Current:	10 A
Weight:	260 g
Input voltage:	24 VDC
Output power:	120 W
Output voltage:	
Number of sockets:	1
Socket type:	Screw Terminal
Length:	70 mm



Sales information

Order code:	HQ-CONV.DC10A
Product description:	Power Converter 24 VDC - DC 12 V 10 A
Packaging:	Blister
Brand name:	HQ



5 412810 032174

Quantity	LxWxH (mm)	Weight
1	140x55x165	296 gr.
48	300x260x580	15150 gr.