



Halogen Lamp E14 Candle 28 W 370 lm 2800 K

General information

Candle-shaped halogen lamp with E14 cap, 370 lumen and a power consumption of 28 watts. It spreads a warm white light with a colour temperature of 2,800 kelvin.

Specifications

Warm-up time to 60% light:	Less than 1 s
Lumen Maintenance Factor:	85 %
No. of lamps:	1
Starting time:	Less than 0.2s
Diameter:	36 mm
Power Factor:	1.00
Colour Rendering Index (Ra):	100
Wattage:	28 W
Rated luminous flux:	370 lm
Dimmable:	Yes
No. of switching cycles:	8000
Energy Class:	D
Energy consumption per 1000 h:	28 kWh
Wattage equivalent:	40 W
Lamp Finish:	Clear
Rated Life time of Lamp:	2000 h
Colour temperature:	2800 K
Lamp Shape:	Candle
Voltage:	230 V
Technology:	Halogen
Light colour:	Warm White
Base:	E14



Sales information

Order code: **HQHE14CAND001**
 Product description: Halogen Lamp E14 Candle 28 W 370 lm 2800 K
 Packaging: Giftbox with eurolock
 Brand name: HQ



Quantity	LxWxH (mm)	Weight
1	42x42x142	29 gr.
10	95x135x220	349 gr.
100	235x280x480	3940 gr.