



Halogen lamp classic GLS E27 42 W 630 lm 2800K

General information

Classic GLS-shaped halogen lamp with E27 cap, 630 lumen and a power consumption of 42 watts. It spreads a warm white light with a colour temperature of 2,800 kelvin.

Specifications

Colour Temperature:	2800 K
Diameter:	56 mm
Dimmable:	Yes
Energy Class:	D
Energy consumption:	42 kWh / 1000h
Glass Style:	Clear
Height:	97 mm
HG:	None mg Milligram
Lamp Shape:	Classic GLS
Lamp Type:	Halogen
Life Span:	2000 h
Light Colour:	Warm White
Lumen:	630 lm
Lumen Maintenance Factor (LMF):	0.85
Power Factor:	1
Ra Value:	100
Replacement Wattage:	60 W
Socket:	E27
Starting Time:	
Switch Cycles:	8000
Voltage:	230 V
Warm Up time 60% brightness:	
Wattage:	42 W



Sales information

Order code: **HQHE27CLAS003**
 Product description: Halogen lamp classic GLS E27 42 W 630 lm 2800K
 Packaging: Giftbox with eurolock
 Brand name: HQ



Quantity	LxWxH (mm)	Weight
1	60x60x140	47 gr.
5	70x130x310	298 gr.
50	325x280x375	3460 gr.