



Halogen lamp capsule G4 5 W 35 lm 2800K

General information

Capsule-shaped halogen lamp with G4 cap, 35 lumen and a power consumption of 5 watts. It spreads a warm white light with a colour temperature of 2,800 kelvin. Price is for 1 box. 1 box contains 2 bulbs

Specifications

Colour Temperature:	2800 K
Diameter:	9 mm
Dimmable:	Yes
Energy Class:	C
Energy consumption:	5 kWh / 1000h
Glass Style:	Clear
Height:	33 mm
HG:	None mg Milligram
Lamp Shape:	Capsule
Lamp Type:	Halogen
Life Span:	2000 h
Light Colour:	Warm White
Lumen:	35 lm
Lumen Maintenance Factor (LMF):	0.85
Power Factor:	1
Ra Value:	100
Socket:	G4
Starting Time:	
Switch Cycles:	8000
Voltage:	12 V
Warm Up time 60% brightness:	
Wattage:	5 W



Sales information

Order code:	HQHG4CAPS001
Product description:	Halogen lamp capsule G4 5 W 35 lm 2800K
Packaging:	Giftbox with eurolock
Brand name:	HQ



Quantity	LxWxH (mm)	Weight
1	45x24x68	11 gr.
25	135x73x232	351 gr.
250	285x260x390	3900 gr.