

LED lamp reflector E14 5.5 W 350 lm 2700K

General information

Reflector-shaped LED lamp with E14 cap, 350 lumen and a very low power consumption of 5.5 watts to replace traditional 50-watt incandescent lamps and gain immediate energy savings.

It spreads a warm white light with a colour temperature of 2,700 kelvin.

Specifications

Lamp Type:	LED
Lamp Shape:	Reflector
Socket:	E14
Wattage:	5.5 W
Voltage:	220 - 240 V
Replacement Wattage:	50 W
Light Colour:	Warm White
Energy Class:	A+
Lumen:	350 lm
Colour Temperature:	2700 K
Life Span:	15000 h
Beam Angle:	36 °
Dimmable:	No
Glass Style:	Reflector
Candela:	900 cd
Energy consumption:	6 kWh / 1000h
Height:	82 mm
Diameter:	50 mm
Warm Up time 60% brightness:	Instant sec.
Switch Cycles:	20000
HG:	None mg Milligram
Power Factor:	0.7
Starting Time:	0 sec.
Ra Value:	80
Lumen Maintenance Factor (LMF):	0.7
Color Consistency (SDCM):	6



Sales information

Order code:	HQLE14REFL001
Product description:	LED lamp reflector E14 5.5 W 350 lm 2700K
Packaging:	Giftbox with eurolock
Brand name:	HQ



Quantity	LxWxH (mm)	Weight
1	55x55x130	66 gr.
10	115x115x275	747 gr.