

LED lamp A67 E27 12 W 1 055 lm 2700K

General information

A67-shaped LED lamp with E27 cap, 1 055 lumen and a very low power consumption of 12 watts to replace traditional 75-watt incandescent lamps and gain immediate energy savings.

It spreads a warm white light with a colour temperature of 2,700 kelvin.

Specifications

Lamp Type:	LED
Lamp Shape:	A67
Socket:	E27
Wattage:	12 W
Voltage:	220 - 240 V
Replacement Wattage:	75 W
Light Colour:	Warm White
Energy Class:	A+
Lumen:	1055 lm
Colour Temperature:	2700 K
Life Span:	15000 h
Beam Angle:	220 °
Dimmable:	No
Glass Style:	Reflector
Energy consumption:	12 kWh / 1000h
Height:	136 mm
Diameter:	67 mm
Warm Up time 60% brightness:	Instant sec.
Switch Cycles:	20000
HG:	None mg Milligram
Power Factor:	0.9
Starting Time:	0 sec.
Ra Value:	80
Lumen Maintenance Factor (LMF):	0.7
Color Consistency (SDCM):	6



Sales information

Order code:	HQLE27A67001
Product description:	LED lamp A67 E27 12 W 1 055 lm 2700K
Packaging:	Giftbox with eurolock
Brand name:	HQ

