

## LED lamp mini globe E27 5 W 350 lm 2700K

### General information

Mini globe-shaped LED lamp with E27 cap, 350 lumen and a very low power consumption of 5 watts to replace traditional 32-watt incandescent lamps and gain immediate energy savings.

It spreads a warm white light with a colour temperature of 2,700 kelvin.

### Specifications

Lamp Type:	LED
Lamp Shape:	Mini Globe
Socket:	E27
Wattage:	5 W
Voltage:	220 - 240 V
Replacement Wattage:	32 W
Light Colour:	Warm White
Energy Class:	A+
Lumen:	350 lm
Colour Temperature:	2700 K
Life Span:	15000 h
Beam Angle:	180 °
Dimmable:	No
Glass Style:	Frosted
Energy consumption:	5 kWh / 1000h
Height:	87 mm
Diameter:	45 mm
Warm Up time 60% brightness:	Instant sec.
Switch Cycles:	20000
HG:	None mg Milligram
Power Factor:	0.7
Starting Time:	0 sec.
Ra Value:	80
Lumen Maintenance Factor (LMF):	0.7
Color Consistency (SDCM):	6



### Sales information

Order code:	<b>HQLE27MINI002</b>
Product description:	LED lamp mini globe E27 5 W 350 lm 2700K
Packaging:	Giftbox with eurolock
Brand name:	HQ



Quantity	LxWxH (mm)	Weight
1	50x50x125	51 gr.
10	110x115x255	585 gr.