



## retro filament LED lamp E27 4 watt 450 lumen 2700 kelvin

### General information

A60-shaped retro filament LED lamp with E27 cap, 450 lumen and a very low power consumption of 4 watts to replace traditional 40-watt incandescent lamps and gain immediate energy savings. It even saves more energy than traditional LED lamps. It spreads a warm white light with a colour temperature of 2,700 kelvin.

### Specifications

|                               |                    |
|-------------------------------|--------------------|
| Warm-up Time to 60% Light:    | Instant full light |
| Lamp Mercury Content:         | 0                  |
| Lumen Maintenance Factor:     | 0.8                |
| Starting Time:                | 0.5s               |
| Colour Rendering Index (Ra):  | 80                 |
| Power Factor:                 | 0.5                |
| Colour temperature:           | 2700               |
| Wattage:                      | 4                  |
| Ball Diameter:                | 60                 |
| Rated Luminous Flux:          | 450                |
| Dimmable:                     | No                 |
| Number of Switching Cycles:   | 15000              |
| Beam Angle:                   | 300                |
| Lamp Shape:                   | A60                |
| Equivalent Watt:              | 40                 |
| Lamp Finish:                  | Clear              |
| Rated Life time of Lamp:      | 15000              |
| Energy Class:                 | A++                |
| Energy Consumption per 1000h: | 4                  |
| Voltage:                      | 220-240 VAC        |
| Technology:                   | Filament LED       |
| Light colour:                 | Warm White         |
| Base:                         | E27                |

### Package contents



### Sales information

|                      |                                                          |
|----------------------|----------------------------------------------------------|
| Order code:          | <b>HQLFE27A60001</b>                                     |
| Product description: | retro filament LED lamp E27 4 watt 450 lumen 2700 kelvin |
| Packaging:           | Giftbox with eurolock                                    |
| Brand name:          | HQ                                                       |



| Quantity | LxWxH (mm)  | Weight   |
|----------|-------------|----------|
| 1        | 62x150x62   | 54 gr.   |
| 10       | 77x255x315  | 636 gr.  |
| 100      | 388x285x650 | 7250 gr. |



## **retro filament LED lamp E27 4 watt 450 lumen 2700 kelvin**

- 1x LED Lamp