

LED lamp MR16 GU10 4W 250 lm 2700K

General information

MR16-shaped LED lamp with GU10 cap, 250 lumen and a very low power consumption of 4 watts to replace traditional 35-watt incandescent lamps and gain immediate energy savings.

It spreads a warm white light with a colour temperature of 2,700 kelvin.

Specifications

Lamp Type:	LED
Lamp Shape:	MR16
Socket:	GU10
Wattage:	4 W
Voltage:	220 - 240 V
Replacement Wattage:	35 W
Light Colour:	Warm White
Energy Class:	A+
Lumen:	250 lm
Colour Temperature:	2700 K
Life Span:	15000 h
Beam Angle:	36 °
Dimmable:	No
Glass Style:	Reflector
Candela:	600 cd
Energy consumption:	4 kWh / 1000h
Height:	54 mm
Diameter:	50 mm
Warm Up time 60% brightness:	Instant sec.
Switch Cycles:	20000
HG:	None mg Milligram
Power Factor:	0.7
Starting Time:	0 sec.
Ra Value:	80
Lumen Maintenance Factor (LMF):	0.7
Color Consistency (SDCM):	6



Sales information

Order code:	HQLGU10MR16002
Product description:	LED lamp MR16 GU10 4W 250 lm 2700K
Packaging:	Giftbox with eurolock
Brand name:	HQ



Quantity	LxWxH (mm)	Weight
1	55x55x100	55 gr.
10	115x90x275	622 gr.