

# Hour meters / timers, electromechanical

Timers, round design

With LED run indicator (AC+DC)

HR 47



The hour meter HR 47 with run indicator feature a very high shock resistance.

These panel-mount counters for round panel cut-outs can be used in many different fields of application. These non-resettable counters are very robust and extremely tamper-proof.



### **Characteristics**

- · 7-digit hour meter
- For voltage ranges 10...80 V DC, 100...130 V AC and 187...264 V AC
- · Magnified large figures
- Protection IP65 on the front and rear sides
- · Suitable for any mounting position
- · Without reset, and thus tamper-proof
- · High shock and impact resistance

#### **Benefits**

- With run indicator (AC version), optional LED (DC version)
- For panel cut-out ø 50.5 mm with front panel dimensions ø 58 mm
- · Simple and secure mounting with screwed clamping clip

### **Applications**

General time measurement, construction machinery and industrial trucks, small appliances, UV lamps, display panels in vehicles, compressors, air-conditioning equipment, etc.

Type series		
Description	Mounting	Туре
Timer, round	Clamping clip fixing, screw-on	HR 47

Accessories					
Counter mounting fixture	For round counters with cut-out ø 53 mm	black	N510199		
Gasket, ø 58 mm	For cut-out ø 50 mm	black	N511182		
Adapter and anti-vibration set	For HR 47, ø 80 mm for cut-out ø 71 mm	black	255319		

Suitable gaskets as well as further accessories can be found in the accessories section or in the accessories area of our website at: www.kuebler.com/accessories.



# Hour meters / timers, electromechanical

## Timers, round design With LED run indicator (AC+DC) HR 47

Technical data				
Electrical connection	screw terminal for flat pin 6.3 x 0.8			
Power consumption 10 80 V DC		max. 720 mW		
100 130 V AC, 6	0 Hz	max. 1.1 VA		
187 264 V AC, 5	0 Hz	approx. 1.2 VA		
Rated voltages AC (50 or 60	Hz)	100 130/187 264 V AC,		
	DC	10 80 V DC		
On time		100 %		
Number of digits	AC	7: 99999.99 h		
	DC	7: 999999.9 h		
Resolution	AC	0.01 h equals 36 s		
	DC	0.1 h equals 6 min		
Count mode		adding		
Height of figures		4 mm		
Colour of figures		white and red on black		
Operating temperature	AC	-25°C +80°C (non-condensing)		
	DC	-20°C +70°C (non-condensing)		
Relative humidity		< 95% (non-condensing)		
Mounting position		any		


Protection		up to IP65, EN 60529
Housing		plastic PC (Polycarbonate)
Accuracy	AC	± 0.02%
	DC	± 0.002%
Weight		approx. 50 g
Run indicator	AC	fast rotating wheel in viewing
		window
	DC	optional LED
Test voltage		2000 V AC , 50 Hz for AC version
EMC	Emitted interference	EN 55011 class B
	Immunity to interference	EN 61000-6-2
Device safety	Designed to	EN 61010 part 1
	Protection class	2
	Application area	Pollution level 2


### Options

Counter for  $\emptyset$  52 mm with screwed clamping bracket or screw thread on request

### Timer, round Type HR 47







### 1 Electrical connection

Front bezel thickness max. 6 mm without having to shorten the clamping bracket

			ArtNo.			
Туре	Display	Voltage	10 80 V DC	100 130 V	187 264 V	
				60 Hz	50 Hz	
HR 47	6 digits	V AC, with run indicator		3.474.901.084 <sup>1)</sup>	3.474.901.075 <sup>1)</sup>	
		V DC, without run indicator	3.474.901.373 <sup>1)</sup>			further types on request
		V DC, with run indicator	3.474.911.373 <sup>1)</sup>			