Self-amalgamating Tapes – Electrical Insulation Mastic

HelaTape Power 650

Features and benefits

- Self-amalgamating insulation compound for sealing and padding cable jackets up to 1 kV
- Easily moulded by hand to conform to irregular shapes even during low temperatures
- · Permanently elastic and resistant to ageing
- Perfect adhesion to metal and all types of cable insulations and jackets
- Provides excellent moisture sealing
- Resistant to salt water, ozone, oil and corrosive chemicals
- Excellent for repairing e.g. damaged cable sheats against moisture ingress, where finishing with some layers of Helatape Flex will do the mechanical protection



www.HellermannTyton.co.uk/HelaTape-cat22



HelaTape Power self-amalgamating mastic is highly flexible.

MATERIAL	Isobutene-Isoprene-Rubber (butyl rubber) (IIR)		
Operating Temperature	-10 °C to +105 °C		
Intermittent Operating Temperature	+130 °C		
Water Absorption	0.1 %		
Volume Resistance	10 ¹⁵ Ω cm		
Dielectric Strength	19.7 kV/mm		



ТҮРЕ	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER650	3.20	38.0	1.5 m	Black (BK)	711-10300

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

