



## Wire Harness Tape – Hand-tearable Cloth Tape

### HelaTape Protect 180

#### Features and benefits

- High quality polyester fabric harnessing tape
- Rubber-based adhesive offers very good heat and media resistance
- High temperature stability from -40 °C to +125 °C
- Temperature resistance tested according to LV312
- Very good resistance against abrasion
- Material is very flexible and tearable by hand
- Excellent ageing resistance, and resistant to rotting in wet or damp conditions such as e.g. white goods and automotive, etc.



*HelaTape Protect 180 is very flexible and used for cable harnessing.*

<b>MATERIAL</b>	Polyester (PET)
<b>Operating Temperature</b>	-40 °C to +125 °C
<b>Adhesion to Steel</b>	3.0 N/10 mm
<b>Adhesion to Backing</b>	3.0 N/10 mm
<b>Elongation at break</b>	15 %
<b>Breaking Strength</b>	65 N/10 mm

HF ✓

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT180	0.18	19.0	25.0 m	Black (BK)	712-10002

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



Add items to your watchlist!  
[www.HT.click/49-411](http://www.HT.click/49-411)

