



Wire Harness Tape – Soft and Flexible Fleece Tape

HelaTape Protect 300

Features and benefits

- Soft polyester fleece harnessing tape
- High noise reduction and very high resistance against abrasion
- Synthetic rubber based adhesive offers good heat and media resistance
- High temperature stability from -40 °C to +105 °C
- Material is very flexible and tearable by hand
- Excellent ageing resistance, and resistant to rotting in wet or damp conditions such as e.g. white goods and automotive, etc.



HelaTape Protect 300 provides high noise reduction and media resistance.

MATERIAL	Polyester (PET)
Operating Temperature	-40 °C to +105 °C, (+105 °C for 500 h)
Adhesion to Steel	2.0 N/10 mm
Adhesion to Backing	2.0 N/10 mm
Elongation at break	10 %
Breaking Strength	30 N/10 mm

HF ✓

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT300	0.30	19.0	25.0 m	Black (BK)	712-10001

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Add items to your watchlist!
www.HT.click/49-413

