Rubber Tubing, Chloroprene

The chloroprene tubings (H) are ideally suited to rigorous environments such as aerospace, mass transit and defence markets.

As the material is highly elastic, it's original size can be expanded 500 % on application and 200 % in continuous use.

To save time and effort when fitting the tubing, try the HellermannTyton K, S and SS three prong tools (see Chapter 6.3) and the Hellerine lubricant (see Chapter 2.3), which are specially designed for use with HellermannTyton chloroprene tubing.

Features and Benefits

- · Highly elastic, easy to fit chloroprene tubing
- Withstands up to 120°C intermittent temperature
- Covers many cable diameters with one size
- Available in cut lengths



H rubber tubing is highly flexible and easy to apply.

MATERIAL	Chloroprene (CR)
Operating Temperature	-65 °C to +95 °C, intermittent 120 °C
Flammability	UL94 HB
Elongation at break	min. 500 %
Specifications	BS-3858 Type 1, BS-4G-198 Part 1 Type 1, DEF STAN 59-15 D2







Chloroprene tubing



ТҮРЕ	Supplied Ø D min.	Wall (WT)	Reel Length	Pack Cont.	Colour	Article-No.
H12BKX100M	1.2	0.70	100 m	100 m	Black (BK)	608-01200
H15BKX100M	1.5	0.80	100 m	100 m	Black (BK)	608-01201
H25BKX100M	2.5	0.80	100 m	100 m	Black (BK)	608-01203
H30BKX100M	3.0	0.80	100 m	100 m	Black (BK)	608-01204
H40BKX100M	4.0	1.00	100 m	100 m	Black (BK)	608-01205
H50BKX100M	5.0	1.00	100 m	100 m	Black (BK)	608-01206
H75BKX25M	7.5	1.30	25 m	25 m	Black (BK)	608-01207

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



TYPE	Supplied Ø D min.	Wall (WT)	Length (L)	Pack Cont.	Colour	Article-No.
H12X20BK	1.2	0.70	20.0	1,000 pcs.	Black (BK)	600-02498
H15X20BK	1.5	0.80	20.0	1,000 pcs.	Black (BK)	600-02929
H25X25BK	2.5	0.80	25.0	1,000 pcs.	Black (BK)	600-02934
H30X25BK	3.0	0.80	25.0	1,000 pcs.	Black (BK)	600-02938
H40X30BK	4.0	1.00	30.0	500 pcs.	Black (BK)	600-02947
H50X25BK	5.0	1.00	25.0	500 pcs.	Black (BK)	600-02949
H75X30BK	7.5	1.30	30.0	250 pcs.	Black (BK)	600-02198

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.



Rubber Tubing, Chloroprene

Helsyn TH





Chloroprene tubing

ТҮРЕ	Supplied Ø D min.	Wall (WT)	Reel Length	Pack Cont.	Colour	Article-No.
TH100BKX25M	10.0	1.00	25 m	25 m	Black (BK)	608-01208
TH120BKX25M	12.0	1.00	25 m	25 m	Black (BK)	608-01209
TH140BKX20M	14.0	1.10	20 m	20 m	Black (BK)	608-01210
TH170BKX20M	17.0	1.20	20 m	20 m	Black (BK)	608-01202

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



TYPE	Supplied Ø D min.	Wall (WT)	Length (L)	Pack Cont.	Colour	Article-No.
TH100X35BK	10.0	1.00	35.0	100 pcs.	Black (BK)	600-02493
TH120X50BK	12.0	1.00	50.0	100 pcs.	Black (BK)	600-02495
TH140X50BK	14.0	1.10	50.0	100 pcs.	Black (BK)	600-02496
TH170X50BK	17.0	1.20	50.0	100 pcs.	Black (BK)	600-02497

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

