



Helawrap cable cover

HWPP for industrial applications

Helawrap is used to bundle and protect cables and wires in the electrical industry, panel building, machine building and many other industrial applications. Helawrap is the time-saving solution for industrial applications.

Features and benefits

- Ideal solution for bundling, protecting and fixing cables
- Quick and effortless to apply
- Good abrasion protection
- Special profile enables branching off cable at any point
- Can be removed and reapplied often
- Available in several colours and sizes
- Handy applicator tool included



www.HellermannTyton.co.uk/HWPP-cat22



Protecting and fixing cables with the Helawrap cable cover and accessory set, for instance in wiring cabinets.

| | |
|------------------------------|---|
| MATERIAL | Polypropylene (PP) |
| Operating Temperature | -60 °C to +110 °C, intermittent +140 °C |
| Flammability | UL 94 HB |

HF ✓

RoHS ✓

| TYPE | Bundle Ø max. | Colour | Reel Length | Application Tool | Article-No. |
|--------|------------------|-------------|----------------|---------------------|-------------|
| HWPP8 | 9 | Black (BK) | 25 m | HAT8 | 161-64101 |
| | 9 | Grey (GY) | 25 m | HAT8 | 161-64102 |
| | 9 | Silver (SR) | 25 m | HAT8 | 161-64103 |
| | 9 | White (WH) | 25 m | HAT8 | 161-64104 |
| HWPP16 | 16 | Black (BK) | 25 m | HAT16 | 161-64201 |
| | 16 | Grey (GY) | 25 m | HAT16 | 161-64202 |
| | 16 | Silver (SR) | 25 m | HAT16 | 161-64203 |
| | 16 | White (WH) | 25 m | HAT16 | 161-64207 |
| HWPP20 | 21 | Black (BK) | 25 m | HAT20 | 161-64301 |
| | 21 | Grey (GY) | 25 m | HAT20 | 161-64302 |
| | 21 | Silver (SR) | 25 m | HAT20 | 161-64303 |
| | 21 | White (WH) | 25 m | HAT20 | 161-64304 |
| HWPP25 | 27 | Black (BK) | 25 m | HAT25 | 161-64401 |
| | 27 | Grey (GY) | 25 m | HAT25 | 161-64402 |
| | 27 | Silver (SR) | 25 m | HAT25 | 161-64403 |
| | 27 | White (WH) | 25 m | HAT25 | 161-64407 |
| HWPP30 | 32 | Black (BK) | 25 m | HAT30 | 161-64501 |
| | 32 | Grey (GY) | 25 m | HAT30 | 161-64502 |
| | 32 | Silver (SR) | 25 m | HAT30 | 161-64503 |
| | 32 | White (WH) | 25 m | HAT30 | 161-64504 |
| HWPP40 | 42 | Black (BK) | 15 m | HAT40 | 161-64601 |

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

ECE R-118

For product specific approvals and specifications please refer to the Appendix.

