

# herelink HX406211 Controller Unit User Manual

---

## HERE LINK Controller Unit

---

**Model:** HX4-06211

**Brand:** HERE LINK

**Frequency:**

SRD for 10MHz: 2409MHz-245971Hz

SRD for 20MHz: 2412MHz- 2462MHz

5180-5320MHZ

5500-5700MHZ

5745-5825MHZ

**Housing:** Plastic Weight: 516g (w. antennas)

**Dimensions:** 217×106.5×31mm (w/o antennas, joysticks )

**Screen:** 5.46 inch, 1080P, 16 million colors, capacitive touch screen

**Audio:** 1 x built-in speaker, 2 x built-in microphone

**Remote control:** 2 x joystick, 1 x wheel, 6 x button (w. backlight), 1 x upper right button

**Communication:** WIFI/GPS 2.4GHz on the controller side

**LED:** 2 x tricolor LED (left, right)

**Interface:** 1 x MicroUSB, 1 x Micro SD card slot (extendable to max. 64GB)

**Antenna:** 1 x detachable directional (5dBi), 1 x detachable Omni-directional (2dBi), built-in WIFI antenna, built-in GPS antenna, external GPS antenna interface

**Power:** 4950mAh built-in Lipo Battery Charging: Support micro USB 5V 2A charging

**Power consumption:** < 4W average (With transmission on, medium screen brightness, WIFI off, GPS off)

