

ULTIMATE
EARS®

HYPERBOOM

Portable Wireless
Bluetooth® Speaker



BRING THE PARTY

Ultimate Ears HYPERBOOM rocks a supermassive sound and extreme bass that takes your party into the stratosphere. Its phenomenal dynamic range brings your tracks to life, rendering every sound level in gorgeous detail. The brainy adaptive EQ reads the room—or patio, or rooftop—and automatically customizes the speaker's sound until it's utterly perfect for the space. Two *Bluetooth*®, one auxiliary and one optical input let you and your friends connect four devices and easily switch between them, so the music never has to stop! With up to a 24 hour rechargeable battery, HYPERBOOM goes all night—and anywhere—from your living room dance-off to the ragin' roof party.

FEATURES

- Supermassive sound + extreme bass
- Easy music sharing with 4 input sources
- Up to 24 hr rechargeable battery life¹
- Adaptive EQ for perfect sound in any space
- Spill and splash proof²
- Connect to any other MEGABOOM, BOOM or HYPERBOOM speakers to Party Up
- One-Touch play/pause/skip directly on speaker
- One-Touch streaming of pre-set custom playlists³
- 45m (150 ft) *Bluetooth*® wireless range
- Pullout carry strap

WHAT'S IN THE BOX

- HYPERBOOM Wireless portable *Bluetooth*® speaker
- Power adaptor
- Documentation (Quick start guide)
- 2-year limited hardware warranty

¹ Actual battery life will vary with use, settings, and environmental conditions.

² IPX4-rated spill and splash proof.

³ One-touch playlist is available for Spotify® on Android, Amazon Music (subscription required), Apple Music® and Deezer® Premium via the BOOM app.

PACKAGE SPECIFICATIONS

| | Single | Case Pack |
|-----------------|---------------|------------------|
| Part # | 984-001591 | N/A |
| UPC | 097855151438 | 00097855151438 |
| Weight | 266.14 oz. | 280.60 oz. |
| Width | 10.24 in. | 10.51 in. |
| Length | 19.53 in. | 10.63 in. |
| Height | 10.12 in. | 20.28 in. |
| Case Pack Count | N/A | 1 single unit |
| Pallet Count | 32 units | 32 case packs |



SYSTEM REQUIREMENTS

Smartphones, tablets and other devices that support *Bluetooth®* and *Bluetooth®* Smart wireless audio profile [Advanced Audio Distribution Profile (A2DP)]

TECH SPECS

BLUETOOTH® WIRELESS RANGE:

- Music playback up to 45m (150 ft)

AUDIO:

- Maximum sound level: 100 dBC
- Drivers: 2 X 4.5" woofers | 2 x 1" tweeters | 2 x 3.5" by 7.5" passive radiators
- Frequency response: 47Hz - 20kHz

CONNECTIVITY:

- Connect and switch between up to 4 devices
- 4 inputs: *Bluetooth®* (2), Aux (1), Optical (1)
- USB Charge Out for phone charging

POWER:

- Rechargeable with up to 24 hours of battery life
- AC power adapter

DIMENSIONS:

- H x W x D: 14.33 x 7.5 x 7.5 in (364 x 190 x 190 mm)
- Weight: 13 lbs (5.9 kg)

SPILL AND SPLASH PROOF—IPX4 RATED