



## Technical Data

27.11.2023

Heat shrinkable tubing 2:1 on a reel  
HIS-PACK

**HIS-PACK-6.4/3.2**

**Article Number 300-30641**



Material:

Polyolefin, cross-linked (PO-X)

Colour:

Brown (BN)

Supplied  $\varnothing$  D min.:

6.4 mm

Recov.  $\varnothing$  d max.:

3.2 mm

Wall (WT):

0.60 mm

Shrink Ratio:

2:1

Longitudinal Change After Shrinkage:

+/-5%

Min. Shrink Temperature - °C:

+100 °C

Test Method

Flammability:

UL 224 VW-1 (except transparent)

Operating Temperature :

-55 °C to +125 °C

Heat Shock Test:

4h/250°C

Behaviour at Heat Shock:

not dripping

Heat Aging Test:

168h/175°C

Dielectric Strength:

20 kV/mm

IEC 243

Insulation Class:

E (VDE 0530)

Tensile Strength:

17 MPa

Elongation at break:

800% (IEC 684 P2)

Water Absorption:

0.15 %

Specifications:

ANSI/UL 224, csa-C22.1, csa-C22.2  
No.198.1



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved