


PASSION FOR POWER.


With or without terminals



- without terminals ٠
- with integrated elastic membranes, which can be removed for cable entry via cable glands, sealing range 6.0-15.0 mm •
- with one cable entry in the bottom, sealing range Ø 6.0-13.0 mm •
- lid fasteners sealable without accessories
 retaining strap and external brackets for wall fixing included
- colour: grey, RAL 7035
- To close opened membranes use grommets type EDK. Degree of protection = IP 66. •

| rated insulation voltage | $U_i = 1000 V a.c./d.c.$ |
|--------------------------|--------------------------|
| material | PP (polypropylene) |
| degree of protection | IP 66 |
| mounting width | 74 mm |
| mounting height | 74 mm |
| max. installation depth | 47 mm |
| width | 93 mm |
| height | 93 mm |
| depth | 62 mm |
| weight | 0,099 kg |
| in accordance with | IEC 60670-22 |

Drawings




Dimension drawing



PASSION FOR POWER.

With or without terminals





PASSION FOR POWER.

With or without terminals

