

TECHNICAL DATA

Fluke i17XX-flex1500 iFlex® Current Clamp



Product overview: Fluke i17XX-flex1500 iFlex® Current Clamp

The Fluke 17XX 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the 173X Energy or Power Logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 17XX iFlex cables are available in 12, 24, and 36 inch models.

Ordering information



i17XX-flex1500

1500A 12 inch iFlex® Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
02/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**