



ICY BOX IB-1124L-C3

1 Bay SATA SSD/HDD DockingStation

Key features

- SATA I/II/III SSD/HDD to USB 3.0
- Connection to host computer via USB 3.0 with up to 5 Gbit/s
- Supports 2.5" and 3.5" SATA drives
- LED ambient illumination
- Plug & Play and HotSwap



Packing content

IB-1124L-C3, USB 3.0 cable (USB Type-B to USB Type-A /Type-C®), Wall power adapter, Manual

Ambiente DockingStation

The neatly shaped body of this DockingStation impresses with a blue ambient light and LED accents and offers a slot for a 2.5" or a 3.5" SSD/HDD. Data transfer rates of up to 5 Gbit/s are possible via the USB 3.0 host connection. Thanks to the USB Type-B to Type-A or Type-C® cable, the DockingStation can be flexibly connected to almost all commonly used computers.

Technical data

Model	IB-1124L-C3
Article no.	60839
EAN code	4250078171751
Brand	ICY BOX
Colour	Black
Material	Plastic
HDD size	2.5"/3.5"
HDD height	Up to 25.4 mm
HDD interface	SATA I/II/III (6 Gbit/s)
HDD capacity	Unlimited
Interface to host computer	USB 3.0 Type-A/Type-C®
Transfer rate	Up to 5 Gbit/s

UASP support	Yes
Plug & Play	Yes
HotSwap	Yes
ON/OFF button	Yes
LED	Power, access, ambient
Power supply	External wall power adapter (12 V/ 2 A)
DC-Plug dimension	5.5 (Ø outside) x 2.1 (Ø inside) x 10 (length)
Operating system	Windows®, macOS®
System requirements	One free USB Type-A or Type-C® port on your host computer. Alternatively one free Thunderbolt™ 3 Type-C® port on your host computer. One free household EU 230 V power socket. The IB-1124L-C3 also works on USB 2.0 interfaces with a data transfer rate of up to 480 Mbit/s.



ICY BOX **IB-1124L-C3** 1 Bay SATA SSD/HDD DockingStation



Ambience for your workplace

The ambient lighting extends once around the enclosure as a blue strip. The blue circular LED not only has a visual effect, but also indicates operation and access of the hard drive. This DockingStation complements your office or home office as a technically reliable design object.



Quickly docked

Plug & Play makes installing hard disks a child's play and HotSwap technology enables easy hard disk replacement without having to switch off the unit. The generously dimensioned hard disk slot allows SSDs/HDDs with a thickness of up to 25.4 mm to be inserted. At the same time, smaller hard disks are held firmly in position by a spring.



Combi-cable

Such a combi-cable is simply useful: the 2-in-1 plug contains both a Type-A and a Type-C® connection; so it is well equipped to connect to your host computer. The 100 cm long cable offers USB specification 3.0 with a data transfer rate of up to 5 Gbit/s.

Logistical data

Packing unit: 20 pcs. / carton
Total weight: 11.5 kg
Gross weight (with packing): 0.520 kg
Net weight: 0.191 kg

Dimension/carton: 510x390x290 mm
Dimension (with packing): 75x130x233 mm
Dimension of article: 160x85x66 mm
Country of origin: China