



ICY BOX IB-AC618

7 Port USB 3.0 Hub with USB charge port

Key features

- Aluminium case
- 7x USB 3.0 Type A connectors incl.
- 1x USB charge port, 5 V / 2.4 A*
- 1x USB 3.0 Type-B connector cable length 80 cm
- Transfer rate up to 5 Gbit/s
- Plug & Play and HotSwap
- Incl. 12 V / 3 A power adapter, USB 3.0 cable for connection to PC

*Nur wenn der angeschlossene PC ausgeschaltet ist oder die USB Verbindung getrennt wird, kann der Anschluss Nr. 7 zum Laden von 5 V USB Geräten mit höherem Stromstärkebedarf (bis zu 2,4 A) verwendet werden.



Packing content
1 x IB-AC618, 1 x USB 3.0 cable Type A to B,
1 x Wall power supply, 4x rubber feet

First: Faster, Second: tenfold, Third: Charging!

Everybody knows how it feels when there is no free USB port. This is where the ICY BOX IB-AC618 is coming in hand. The USB hub creates seven further ports and therefore is fitting for home use as well as the professional use. This is added to the fact his hubs metal enclosure is made our of robust aluminium, so fast nothing shakes in the truest sense of the word.

USB 3.0 has the bandwidth of up to 5 GBit / second. With the help of the ICY BOX IB-AC618 this can be achieved seven times. USB 3.0 is downwards compatible,

Technical data

 Model
 IB-AC618

 Article no.
 70418

 EAN code
 4250078160182

 Brand
 ICY BOX

 Colour
 Black

 Material
 Aluminium

Interface to host computer 1x USB 3.0 Typ B
Interface to devices 7x USB 3.0 Typ A

HotSwap Yes Plug & Play Yes

 Transfer rate
 Up to 5 Gbit/s

 LED
 Power on + HDD access

 Power connector
 100-240 V to 12 V / 3 A







ICY BOX **IB-AC618**7 Port USB 3.0 Hub with USB charge port



Seven times powerful

When all the USB 3.0 ports on the PC are aleady used and the need arises to connect an additional device rgently, this candidate could be the perfect assistance. One USb 3.0 port on the PC must be made free, but or that, seven ports are at your disposal in a greater ease of use as before on the PC.



They are not all the same

One USB 3.0 port is a bit different than the others. Number 7 is the so called "Charging port", with it, charging a mobile device or a recharbable battery with 5V / 2.4A is made fast and effecient since the normal USb 3.0 ports provide only 0.9 Amper.



A robust companion

The IB-AC618 does not tremble so fast. The high quality aluminium dissiapte the inner heat to the outside of the device and provide a perfect passive cooling. Additionally the material is light and is hard to scratch, which makes it a perfect companion for transport as well as stationary.

Logistical data

 Packing unit:
 15 pcs./carton

 Total weight:
 8.5 kg/carton

 Gross weight (with packing):
 0.507 kg

 Net weight:
 0.122 kg

Dimension/carton:
Dimension (with packing):
Dimension of article:
Country of origin:

423x333x243 mm 100x80x200 mm 113x46x26x mm





