

ICY BOX IB-EW205B-T

Electric height adjustable sit /stand desk frame with digital memory touch panel

Key features

- Programmable digital memory touch controller for
- Up and down movement
- Three programmable height settings
- Timer for sit/stand reminder
- Collision avoidance system to protect against accidents and injuries
- Two motors for loads up to 125 kg with overload protection
- Electrical height adjustment from 62 cm to 128 cm
- Height-adjustable feet with rubber protection to compensate for unevenness
- Ideal for office and home office
- For ergonomic work
- Cable management tray against cable tangle: for a tidy and structured workplace
- Switching power supply for low power consumption and optimum efficiency




Packing content IB-EW205B-T, accessory kit (table top not included)

Model IB-EW205B-T Article no 60866 EAN Colour Material Supported weight Height adjustment Numbers of motor Lifting speed Noise emission Numbers of leg Numbers of stages Height adjustment range Height levels Width adjustment range **Control panel** Safety Power supply Power Cord Length

BIFMA Compliant

Technical data

4250078171997 Black Table base: steel Up to 125 kg 660 mm, automatically 2 Up to 38 mm/s ≤ 50 dB 2 From 620 mm to 1280 mm Continuously variable From 1000 mm to 1700 mm Digital memory touch controller Anti-collision sensor Input: 100 - 240 V, 50/60 Hz, 3 A Output: 32 V, 6 A 3 m Meets and exceeds BIFMA X5.5-2014 standard for stability and durability







ICY BOX IB-EW205B-T Electric height adjustable sit / stand desk frame with digital memory touch panel



Discover ways to work healthier

Studies suggest that switching from sitting to standing offers several health benefits and can increase productivity. With the IB-EW206B-T, you can now easily achieve the perfect balance between sitting and standing throughout the workday.

We have the simple option to create a high quality sit/stand desk solution if you want a solution without unnecessary accessories and high costs. It is perfect for offices, schools, homes and most workspaces and integrates your existing tabletops.




Easy control

We have the powerful, smooth-running, stable, quiet and continuously adjustable table base with two motors for trouble-free height adjustment with up to 38 mm per second lifting speed. 3-stage extendable table legs provide a split-second transition from sitting to standing at the touch of a finger.

Thanks to the digital LED control unit, adjustments can be made at the touch of a button. Three programmable memory presets store your desired height settings and provide automatic reminders to switch between standing and sitting for regular exercise.

The sturdily built steel table legs are adjustable via a telescopic height adjustment. This ensures that the transition to your ideal, ergonomic position is made in seconds with a simple touch. The dual motor offers better stabilisation, higher load capacity and low running noise, so you can go about your work undisturbed.



Logistical data Packing unit: Total weight: Gross weight (with packing): Net weight: 31.0 kg

1 pcs./carton 34.0 kg/carton 34.0 kg

Dimension/carton: Dimension (with packing): Dimension of article: Country of origin:

300x1112x225 mm 300x1112x225 mm 620x1700x1280 mm China

Dual electric lift system

RaidSonic Technology GmbH • Kurt-Fischer-Straße 50 • 22926 Ahrensburg / Germany Telephone: +49-(0)4102 - 468 900 (Sales) • Fax: +49-(0)4102 - 468 901 • info@raidsonic.de • www.icybox.de Offers and deliveries are only done under our General Terms and Conditions. Errors and omissions excepted.

