



ICY BOX IB-EWA 111 - FT

Ergonomic footrest

Key features

- Tilt angle from +40° to -6°
- Three height settings: 10 cm/12 cm/15 cm
- Increases sitting comfort
- Improves blood circulation by elevating the legs
- Comfortable for every body size due to tilt adjustment
- Non-slip feet for good stability



Packing content

- 1x IB-EWA 111 - FT
- 1x Quick installation guide

A wellness accessory

IB-EWA 111-FT is an ergonomic footrest that can be used in many ways thanks to its variably adjustable inclination. Support your feet on the knobbed surface and thereby improve the circulation of the extremities. Used without shoes, the knobs on the soles of the feet act like a light acupressure. By propping your feet up, you are encouraged to adopt a more ergonomic sitting position, which encourages productivity, reduces stress and prevents fatigue.

Technical data

Model	IB-EWA 111-FT
Article no.	60919
EAN	4250078172505
Colour	Black
Material	Metal, plastic
Tilt angle	+40° to -6°





ICY BOX **IB-EWA111-FT** Ergonomic footrest



Posture improvement

A footrest can improve your posture in the long run. With our IB-EWA111-FT, which can be flexibly adjusted in the angle of inclination, you automatically adopt a more ergonomic sitting position and immediately provide yourself with noticeable comfort.



Prevent fatigue

The footrest has a non-slip surface and thus offers good grip, whether working with or without shoes. The surface is also provided with nubs, which ensures better blood circulation to the feet when used without shoes: also a means to prevent premature fatigue.



Robust materials

The footrest is solidly made of steel and high-quality plastic. All materials are optimally adapted to the functions to be performed, i.e. the footrest is stable, the angle of inclination can be adjusted well and the surface is non-slip. All this is reflected in the haptics.

Logistical data

Packing unit: 5 pcs./carton
Total weight: 11.600 kg/carton
Gross weight (with packing): 2.090 kg
Net weight: 1.775 kg

Dimension/carton: 520x380x520 mm
Dimension (with packing): 500x360x100 mm
Dimension of article: 495x355x95 mm
Country of origin: Taiwan