

1 ft USB to RS232 Serial DB9 Adapter Cable with COM Retention

Product ID: ICUSB232PRO



The ICUSB232PRO 1 ft USB to RS232 Serial DB9 Adapter Cable with COM Retention offers a professional grade solution for connecting legacy or industrial RS232 serial devices to a laptop or desktop computer through USB - eliminating the expense of upgrading serial peripherals for compatibility.

A time-saving and convenient USB/Serial solution, the adapter retains assigned serial COM port values in nonvolatile memory, allowing the same values to automatically be assigned to the adapter serial port if disconnected and reconnected, or disconnected from one USB port and installed in another.

A versatile connectivity solution that bridges legacy serial peripheral devices with newer USB-capable computers, the USB to Serial adapter offers broad operating system compatibility including Windows, Linux and Mac OS, for easy integration into mixed environments.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports



Features

- COM Port assignments maintained across reboot
- Supports remote wake up and power management control
- Powered by an available USB port no external power adapter required
- Provides dual buffers for upstream and downstream data transfer
- Supports automatic handshake mode
- Supports data transfer rates of up to 920kpbs
- USB to Straight-Through RS232 Serial Adapter

Hardware		
	Warranty	2 Years
	Ports	1
	Interface	Serial
	Bus Type	USB 2.0
	Port Style	Cable Adapters
	Chipset ID	Prolific - PL2303
Performance		
	Serial Protocol	RS-232
	Max Baud Rate	921.6 Kbps
Connector(s)		
	Connector Type(s)	DB-9 (9 pin, D-Sub)
		USB Type-A (4 pin) USB 2.0
Software		
	OS Compatibility	Windows PocketPC 2003 / 2000, Windows Mobile 5/6, CE 4.2/5.2, Embedded System 2009, XP Embedded, POS Ready 2009, 98SE, 2000, ME, XP, Vista, 7, 8, 8.1, 10
		Windows Server 2003, 2008 R2, 2012, 2016, 2019

macOS 10.6 to 10.15, 11.0



Linux 2.4.x to 4.19.x <i>LTS Versions only</i>

Special Notes / Requirements

System and Cable Requirements

PC with an available USB 1.1 (or above) port

Environmental

Operating Temperature -10C to 80C (14F to 176F)

Storage Temperature -20C to 100C (-4F to 212F)

Humidity 5~85% RH

Physical Characteristics

Color Black

Material Plastic

Cable Length 12.0 in [30.5 cm]

Product Length 15.7 in [40 cm]

Product Width 1.3 in [34 mm]

Product Height 0.6 in [15 mm]

Weight of Product 1.1 oz [30 g]

Packaging Information

Package Length 6.9 in [17.5 cm]

Package Width 5.7 in [14.5 cm]

Package Height 1.2 in [30 mm]

Shipping (Package)

Weight

3.4 oz [97 g]

What's in the Box

Included in Package USB to Serial Adapter

Instruction Manual

Driver CD



*Product appearance and specifications are subject to change without notice.