

1 Port USB to RS232 DB9 Serial Adapter Cable - M/M

Product ID: ICUSB232V2



The ICUSB232V2 1 Port USB to Serial Adapter converts a USB port into an RS232 DB9 serial port to connect to, monitor, and control a serial device.

Supporting data transfer rates up to 921.6 Kbps, the USB to serial cable is a convenient and cost-saving solution for providing serial connectivity to devices such as point-of-sale terminals, serial modems, industrial equipment, and a wide variety of other RS232 peripherals.

The USB to RS232 converter is easy to install and offers broad operating system compatibility, including Windows 8 and later, Linux and Mac OS, for easy integration into mixed environments.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect and program LED and digital signage boards
- Connect, monitor and control industrial/automotive sensors and other sensitive equipment
- Connect bar code scanners, receipt printers and other point of sale devices

Features



- USB to Straight-Through RS232 DB9 Serial Adapter
- Compatible with Windows 8 and later, Mac OS, and Linux
- High-speed 921.6Kbps Baud Rate
- USB-powered no external power adapter required
- Compatible with USB 1.1 or higher ports
- Single cable, small footprint design for portability

н	2	ra	VA.	12	re

Warranty 3 Years

Ports 1

Interface Serial

Bus Type USB 2.0

Port Style Cable Adapters

Industry Standards USB 1.1/2.0

RS232

Chipset ID Prolific - PL2303RA

Performance

Serial Protocol RS-232

Max Baud Rate 921.6 Kbps

Data Bits 5, 6, 7, 8

FIFO 512 Bytes

Flow Control None, Xon/Xoff, RTS/CTS, DTR/DSR

Parity Odd, Even, Mark, Space, or None Parity Modes

Stop Bits 1, 1.5, 2

MTBF 30,000 Hours

Connector(s)

Connector A USB Type-A (4 pin) USB 2.0



	Connector B	DB-9 (9 pin, D-Sub)		
Software				
	OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10		
		Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019		
		macOS 9.x, 8.x, 10.6 to 10.15, 11.0		
		Linux 2.4.31 to 4.11.x <i>LTS Versions Only</i>		
	Microsoft WHQL Certified	Yes		
Special Notes / Requirements				
	System and Cable Requirements	One available USB 1.1 (or above) port		
Environmental				
	Operating Temperature	0C to 60C (32F to 140F)		
	Storage Temperature	-20C to 80C (-4F to 176F)		
	Humidity	0~65% RH		
Physical Characteristics				
	Color	Black		
	Material	Plastic		
	Product Length	16.9 in [43.0 cm]		
	Product Width	1.4 in [35.0 mm]		
	Product Height	0.8 in [20.0 mm]		
	Weight of Product	1.4 oz [40.0 g]		
Packaging Information				
	Package Length	8.7 in [22.0 cm]		
	Package Width	7.9 in [20.0 cm]		
	Package Height	0.8 in [21.0 mm]		
	Shipping (Package) Weight	2.0 oz [56.0 g]		



What's in the Box

Included in Package USB to RS232 Adapter

Instruction Manual

^{*}Product appearance and specifications are subject to change without notice.