

# IDXPERT & LABXPERT Labels to M-Series Labels Cross-Reference Guide

Improve your labeling efficiency when you trade up from an IDXPERT or LABXPERT printer, to a new Brady portable printer. Find your replacement material in the reference chart below:

Colour	Width (mm)	Height (mm/m)	Wire Dia. Range (mm)	IDXPERT Order Reference	M-Series Order Reference	Width (mm)	Height (mm/m)	Wire Dia. Range (mm)	Printer Compatibility
<b>B-342 PermaSleeve® Wire Markers</b>									
White	3.18	25.40 mm	1.17 to 2.79	XPS-125-1	M-125-1-342	3.18	25.40 mm	1.17 to 2.79	BMP51, 53
White	3.18	2.44 m	1.17 to 2.79	XPS-125-CONT	MC-125-342	3.18	2.13 m	1.17 to 2.79	BMP41, 51, 53
White	4.75	25.40 mm	1.57 to 3.81	XPS-187-1	M-187-1-342	4.75	25.40 mm	1.57 to 3.81	BMP51, 53
White	4.75	2.44 m	1.57 to 3.81	XPS-187-CONT	MC-187-342	4.75	2.13 m	1.57 to 3.81	BMP41, 51, 53
White	6.35	25.40 mm	2.39 to 5.46	XPS-250-1	M-250-1-342	6.35	25.40 mm	2.39 to 5.46	BMP51, 53
White	6.35	2.44 m	2.39 to 5.46	XPS-250-CONT	MC-250-342	6.35	2.13 m	2.39 to 5.46	BMP41, 51, 53
White	9.53	25.40 mm	3.18 to 8.13	XPS-375-1	M-375-1-342	9.53	25.40 mm	3.18 to 8.13	BMP51, 53
White	9.53	2.44 m	3.18 to 8.13	XPS-375-CONT	MC1-375-342	9.53	2.13 m	3.18 to 8.13	BMP41, 51, 53
Yellow	3.18	2.44 m	1.17 to 2.79	XPS-125-CONT-YL-BK	MC-125-342-YL	3.18	2.13 m	1.17 to 2.79	BMP41, 51, 53
Yellow	4.75	2.44 m	1.57 to 3.81	XPS-187-CONT-YL-BK	MC-187-342-YL	4.75	2.13 m	1.57 to 3.81	BMP41, 51, 53
Yellow	6.35	2.44 m	2.39 to 5.46	XPS-250-CONT-YL-BK	MC-250-342-YL	6.35	2.13 m	2.39 to 5.46	BMP41, 51, 53
<b>B-422 Polyester</b>									
White	9.53	9.14 m	-	XC-375-422	MC-375-422	9.53	7.62 m	-	BMP41, 51, 53
White	12.07	9.14 m	-	XC-475-422	MC-475-422	12.07	7.62 m	-	BMP41, 51, 53
White	12.70	12.70 mm	-	X-7-422	M-7-422	12.70	12.70 mm	-	BMP41, 51, 53
White	12.70	9.14 m	-	XC-500-422	MC-500-422	12.70	7.62 m	-	BMP41, 51, 53
White	15.88	9.14 m	-	XC-625-422	MC-625-422	15.88	7.62 m	-	BMP41, 51, 53
White	25.40	12.70 mm	-	X-17-422	M-47-422	25.40	12.70 mm	-	BMP41, 51, 53
White	25.40	9.14 m	-	XC-1000-422	MC1-1000-422	25.40	7.62 m	-	BMP41, 51, 53
White	38.10	12.70 mm	-	X-29-422	M-89-422	12.70	38.10 mm	-	BMP41, 51, 53
White	38.10	19.05 mm	-	X-30-422	M-90-422	38.10	19.05 mm	-	BMP41, 51, 53
<b>B-428 Metallized Polyester</b>									
Lt. Gray	25.40	12.70 mm	-	X-17-428-SV-BK	M-47-428	25.40	12.70 mm	-	BMP41, 51, 53
Lt. Gray	28.70	12.70 mm	-	X-24-428-SVBB-BK	M-92-428-BB	28.70	12.70 mm	-	BMP41, 51, 53
Lt. Gray	38.10	12.70 mm	-	X-29-428-SV-BK	M-29-428	12.70	38.10 mm	-	BMP51, 53
Lt. Gray	50.80	25.40 mm	-	X-20-428-SV-BK	M-60-428	50.80	25.40 mm	-	BMP41, 51, 53

## IDXPERT & LABXPERT Labels to M-Series Labels Cross-Reference Guide

Colour	Width (mm)	Height (mm/m)	Secondary Label (mm)	IDXPERT Order Reference	M-Series Order Reference	Width (mm)	Height (mm/m)	Secondary Label (mm)	Printer Compatibility
<b>B-481 Polyester</b>									
White	19.05	22.86 mm	-	X-194-481	M-194-481	22.86	19.05 mm	-	BMP51, 53
White	22.86	22.86 mm	-	X-97-481	M-97-481	22.86	22.86 mm	-	BMP51, 53
<b>B-483 Polyester</b>									
White	25.40	12.70 mm	-	X-17-483	M-47-483	25.40	12.70 mm	-	BMP41, 51, 53
White	50.80	12.70 mm	-	X-61-483	M-61-483	50.80	12.70 mm	-	BMP41, 51, 53
White	50.80	25.40 mm	-	X-20-483	M-60-483	50.80	25.40 mm	-	BMP41, 51, 53
<b>B-488 Polyester</b>									
White	22.86	22.86 mm	-	X-97-488	M-97-488	22.86	22.86 mm	-	BMP51, 53
White	48.26	6.35 mm	-	X-81-488	M-81-488	48.26	6.35 mm	-	BMP51, 53
<b>B-490 Polyester</b>									
White	12.70	41.91 mm	-	X-124-490	M-124-490	41.91	12.70 mm	-	BMP51, 53
White	15.24	45.72 mm	-	X-126-490	M-126-490	45.72	15.24 mm	-	BMP51, 53
White	25.40	44.45 mm	-	X-125-490	M-125-490	44.45	25.40 mm	-	BMP51, 53
White	31.75	9.53 mm	-	X-112-490	M-112-490	31.75	9.53 mm	-	BMP51, 53
White	38.10	95.25 mm	-	X-114-490	M-114-490	95.25	38.10 mm	-	BMP51, 53
<b>B-492 Polyester</b>									
White	6.35	31.75 mm	-	X-155-492	M-155-492	31.75	6.35 mm	-	BMP51, 53
White	9.53 dia.	-	-	X-82-492	M-82-492	9.53 dia.	-	-	BMP51, 53
White	12.70	9.14 m	-	XC-500-492	MC-500-492	12.70	7.62 m	-	BMP51, 53
White	12.70 dia.	-	-	X-83-492	M-83-492	12.70 dia.	-	-	BMP51, 53
White	20.96	9.53 mm	-	X-130-492	M-130-492	9.53	20.96 mm	-	BMP51, 53
White	22.86	25.40 mm	-	X-156-492	M-156-492	25.40	22.86 mm	-	BMP51, 53
White	25.40	9.53 mm	9.53 dia.	X-118-492	M-118-492	9.53	25.40 mm	9.53 dia.	BMP51, 53
White	25.40	9.53 mm	9.53 dia.	X-120-492	M-120-492	12.70	25.40 mm	9.53 dia.	BMP51, 53
White	25.40	12.70 mm	-	X-131-492	M-131-492	12.70	25.40 mm	-	BMP51, 53
White	25.40	12.70 mm	11.18 dia.	X-117-492	M-117-492	25.40	12.70 mm	11.18 dia.	BMP51, 53
White	48.26	25.40 mm	-	X-78-492	M-78-492	48.26	25.40 mm	-	BMP51, 53
<b>B-498 Cloth</b>									
White	6.10	6.10 m	-	XC-240-498	MC-240-498	6.10	4.88 m	-	BMP41, 51, 53
White	8.08	6.10 m	-	XC-318-498	MC-318-498	8.08	4.88 m	-	BMP41, 51, 53
White	9.53	6.10 m	-	XC-375-498	MC-375-498	9.53	6.10 m	-	BMP41, 51, 53
White	12.70	12.70 mm	-	X-7-498	M-7-498	12.70	12.70 mm	-	BMP41, 51, 53
White	12.70	19.05 mm	-	X-11-498	M-11-498	19.05	12.70 mm	-	BMP41, 51, 53
White	12.70	25.40 mm	-	X-163-498	M-163-498	25.40	12.70 mm	-	BMP41, 51, 53
White	12.70	38.10 mm	-	X-162-498	M-91-498	25.40	38.10 mm	-	BMP41, 51, 53
White	19.05	25.40 mm	-	X-18-498	M-48-498	19.05	25.40 mm	-	BMP41, 51, 53
White	25.40	12.70 mm	-	X-131-498	M-131-498	12.70	25.40 mm	-	BMP41, 51, 53
White	25.40	25.40 mm	-	X-19-498	M-49-498	25.40	25.40 mm	-	BMP41, 51, 53
White	25.40	31.75 mm	-	X-103-498	M-103-498	25.40	31.75 mm	-	BMP51, 53
White	25.40	38.10 mm	-	X-31-498	M-91-498	25.40	38.10 mm	-	BMP41, 51, 53
White	25.40	48.26 mm	-	X-78-498	M-128-498	25.40	48.26 mm	-	BMP51, 53
White	25.40	101.60 mm	-	X-23-498	M-128-498	25.40	48.26 mm	-	BMP51, 53

## IDXPERT & LABXPRT Labels to M-Series Labels Cross-Reference Guide

Colour	Width (mm)	Height (mm/m)	Secondary Label (mm)	IDXPERT Order Reference	M-Series Order Reference	Width (mm)	Height (mm/m)	Secondary Label (mm)	Printer Compatibility
<b>B-499 Nylon</b>									
White	9.53	6.10 m	-	XC-375-499	MC-375-499	9.53	4.88 m	-	BMP41, 51, 53
White	9.53 dia.	-	-	X-82-499	M-82-499	9.53 dia.	-	-	BMP51, 53
White	12.70	25.40 mm	-	X-131-499	M-131-499	12.70	25.40 mm	-	BMP41, 51, 53
White	12.70	6.10 m	-	XC-500-499	MC-500-499	12.70	4.88 m	-	BMP41, 51, 53
White	12.70 dia.	-	-	X-83-499	M-83-499	12.70 dia.	-	-	BMP51, 53
White	19.05	12.70 mm	-	X-11-499	M-11-499	12.70	19.05 mm	-	BMP41, 51, 53
White	19.05	6.10 m	-	XC-750-499	MC-750-499	19.05	4.88 m	-	BMP41, 51, 53
White	20.96	9.53 mm	-	X-130-499	M-130-499	9.53	20.96 mm	-	BMP41, 51, 53
White	22.86	12.70 mm	-	X-84-499	M-84-499	22.86	12.70 mm	-	BMP51, 53
White	25.40	9.53 mm	9.53 dia.	X-118-499	M-118-499	9.53	25.40 mm	9.53 dia.	BMP51, 53
White	25.40	12.70 mm	9.53 dia.	X-120-499	M-120-499	12.70	25.40 mm	9.53 dia.	BMP51, 53
White	25.40	12.70 mm	11.18 dia.	X-117-499	M-117-499	25.40	12.70 mm	-	BMP51, 53
White	25.40	48.26 mm	-	X-78-499	M-128-499	25.40	48.26 mm	-	BMP41, 51, 53
White	25.40	6.10 m	-	XC-1000-499	MC-1000-499	25.40	4.88 m	-	BMP51, 53
White	31.75	38.10 mm	-	X-132-499	M-132-499	38.10	31.75 mm	-	BMP51, 53
White	38.10	12.70 mm	-	X-162-499	M-131-499	12.70	25.40 mm	-	BMP41, 51, 53
White	38.10	19.05 mm	-	X-30-499	M-131-499	12.70	25.40 mm	-	BMP41, 51, 53
White	38.10	38.10 mm	-	XF-152-499	M-152-499	38.10	31.75 mm	-	BMP51, 53
White	57.15	25.40 mm	-	XF-151-499	M-141-499	25.40	57.15	-	BMP41, 51, 53
Yellow	9.53 dia.	-	-	X-82-499-YL-BK	M-82-499-YL-BK	9.53 dia.	-	-	BMP51, 53
Yellow	12.70 dia.	-	-	X-83-499-YL-BK	M-83-499-YL-BK	12.70 dia.	-	-	BMP51, 53
<b>B-595 Vinyl</b>									
Blk on Wht	12.70	9.14 m	-	XC-500-595-WT-BK	MC-500-595-WT-BK	12.70	7.62 m	-	BMP41, 51, 53
Blk on Wht	19.05	9.14 m	-	XC-750-595-WT-BK	MC-750-595-WT-BK	19.05	7.62 m	-	BMP41, 51, 53
Blk on Wht	25.40	9.14 m	-	XC-1000-595-WT-BK	MC1-1000-595-WT-BK	25.40	7.62 m	-	BMP41, 51, 53
Blk on Wht	38.10	9.14 m	-	XC-1500-595-WT-BK	MC-1500-595-WT-BK	38.10	7.62 m	-	BMP51, 53
Blk on Clear	12.70	7.62 m	-	XC-500-595-CL-BK	MC-500-595-CL-BK	12.70	6.10 m	-	BMP41, 51, 53
Blk on Clear	19.05	9.14 m	-	XC-750-595-CL-BK	MC-750-595-CL-BK	19.05	6.10 m	-	BMP41, 51, 53
Blk on Clear	25.40	7.62 m	-	XC-1000-595-CL-BK	MC1-1000-595-CL-BK	25.40	6.10 m	-	BMP41, 51, 53
Blk on Clear	38.10	7.62 m	-	XC-1500-595-CL-BK	MC-1500-595-CL-BK	38.10	6.10 m	-	BMP51, 53
Red on Wht	12.70	9.14 m	-	XC-500-595-WT-RD	MC-500-595-WT-RD	12.70	7.62 m	-	BMP41, 51, 53
Red on Wht	19.05	9.14 m	-	XC-750-595-WT-RD	MC-750-595-WT-RD	19.05	7.62 m	-	BMP41, 51, 53
Red on Wht	25.40	9.14 m	-	XC-1000-595-WT-RD	MC1-1000-595-WT-RD	25.40	7.62 m	-	BMP41, 51, 53
Red on Wht	38.10	9.14 m	-	XC-1500-595-WT-RD	MC-1500-595-WT-RD	38.10	7.62 m	-	BMP51, 53
Blk on Ylw	12.70	9.14 m	-	XC-500-595-YL-BK	MC-500-595-YL-BK	12.70	7.62 m	-	BMP41, 51, 53
Blk on Ylw	19.05	9.14 m	-	XC-750-595-YL-BK	MC-750-595-YL-BK	19.05	7.62 m	-	BMP41, 51, 53
Blk on Ylw	25.40	9.14 m	-	XC-1000-595-YL-BK	MC1-1000-595-YL-BK	25.40	7.62 m	-	BMP41, 51, 53
Blk on Ylw	38.10	9.14 m	-	XC-1500-595-YL-BK	MC-1500-595-YL-BK	38.10	7.62 m	-	BMP51, 53
Blk on Org	12.70	9.14 m	-	XC-500-595-OR-BK	MC-500-595-OR-BK	12.70	7.62 m	-	BMP41, 51, 53
Blk on Org	19.05	9.14 m	-	XC-750-595-OR-BK	MC-750-595-OR-BK	19.05	7.62 m	-	BMP41, 51, 53
Blk on Org	25.40	9.14 m	-	XC-1000-595-OR-BK	MC1-1000-595-OR-BK	25.40	7.62 m	-	BMP41, 51, 53
Blk on Org	38.10	9.14 m	-	XC-1500-595-OR-BK	MC-1500-595-OR-BK	38.10	7.62 m	-	BMP51, 53
Wht on Blu	12.70	9.14 m	-	XC-500-595-BL-WT	MC-500-595-BL-WT	12.70	7.62 m	-	BMP41, 51, 53
Wht on Blu	19.05	9.14 m	-	XC-750-595-BL-WT	MC-750-595-BL-WT	19.05	7.62 m	-	BMP41, 51, 53
Wht on Blu	25.40	9.14 m	-	XC-1000-595-BL-WT	MC1-1000-595-BL-WT	25.40	7.62 m	-	BMP41, 51, 53
Wht on Blu	38.10	9.14 m	-	XC-1500-595-BL-WT	MC-1500-595-BL-WT	38.10	7.62 m	-	BMP51, 53
Wht on Grn	12.70	9.14 m	-	XC-500-595-GN-WT	MC-500-595-GN-WT	12.70	7.62 m	-	BMP41, 51, 53
Wht on Grn	19.05	9.14 m	-	XC-750-595-GN-WT	MC-750-595-GN-WT	19.05	7.62 m	-	BMP41, 51, 53
Wht on Grn	25.40	9.14 m	-	XC-1000-595-GN-WT	MC1-1000-595-GN-WT	25.40	7.62 m	-	BMP41, 51, 53
Wht on Grn	38.10	9.14 m	-	XC-1500-595-GN-WT	MC-1500-595-GN-WT	38.10	7.62 m	-	BMP51, 53
Wht on Red	12.70	9.14 m	-	XC-500-595-RD-WT	MC-500-595-RD-WT	12.70	7.62 m	-	BMP41, 51, 53
Wht on Red	19.05	9.14 m	-	XC-750-595-RD-WT	MC-750-595-RD-WT	19.05	7.62 m	-	BMP41, 51, 53
Wht on Red	25.40	9.14 m	-	XC-1000-595-RD-WT	MC1-1000-595-RD-WT	25.40	7.62 m	-	BMP41, 51, 53
Wht on Red	38.10	9.14 m	-	XC-1500-595-RD-WT	MC-1500-595-RD-WT	38.10	7.62 m	-	BMP51, 53

## IDXPERT Labels to M-Series Labels Cross-Reference Guide

Colour	Width (mm)	Height (mm/m)	Print-On Area (mm)	IDXPERT Order Reference	M-Series Order Reference	Width (mm)	Height (mm/m)	Print-On Area (mm)	Printer Compatibility
<b>B-427 Self-Laminating Vinyl</b>									
All White	6.35	27.94 mm	6.35	X-105-427-AW	M-135-427-AW	6.35	27.94 mm	6.35	BMP51, 53
Clear/White	12.70	19.05 mm	9.53	XSL-11-427	M-11-427	12.70	19.05 mm	9.53	BMP41, 51, 53
Clear/White	12.70	25.40 mm	9.53	XSL-17-427	M-47-427	9.53	25.40 mm	9.53	BMP41, 51, 53
Clear/White	12.70	31.75 mm	9.53	XSL-102-427	M-102-427	12.70	31.75 mm	9.53	BMP41, 51, 53
Clear/White	12.70	38.10 mm	12.70	XSL-29-427	M-89-427	12.70	38.10 mm	12.70	BMP41, 51, 53
Clear/White	19.05	25.40 mm	9.53	XSL-18-427	M-48-427	9.53	25.40 mm	9.53	BMP41, 51, 53
Clear/White	19.05	38.10 mm	12.70	XSL-30-427	M-90-427	12.70	38.10 mm	12.70	BMP41, 51, 53
Clear/White	25.40	19.05 mm	9.53	XSL-96-427	M-136-427	25.40	19.05 mm	9.53	BMP41, 51, 53
Clear/White	25.40	25.40 mm	9.53	XSL-19-427	M-49-427	25.40	9.53 mm	9.53	BMP41, 51, 53
Clear/White	25.40	31.75 mm	12.70	XSL-103-427	M-143-427	25.40	31.75 mm	12.70	BMP41, 51, 53
Clear/White	25.40	38.10 mm	12.70	XSL-31-427	M-91-427	12.70	38.10 mm	12.70	BMP41, 51, 53
Clear/White	25.40	63.50 mm	19.05	XSL-21-427	M-51-427	25.40	63.50 mm	19.05	BMP41, 51, 53
Clear/White	25.40	101.60 mm	25.40	XSL-23-427	M-53-427	25.40	101.60 mm	25.40	BMP41, 51, 53
Clear/White	38.10	31.75 mm	12.70	XSL-115-427	M-115-427	38.10	31.75 mm	12.70	BMP51, 53
Clear/White	38.10	38.10 mm	12.70	XSL-32-427	M-32-427	38.10	38.10 mm	12.70	BMP51, 53
Clear/White	38.10	63.50 mm	19.05	XSL-116-427	M-116-427	38.10	63.50 mm	19.05	BMP51, 53
Clear/White	38.10	101.60 mm	25.40	XSL-33-427	M-33-427	38.10	101.60 mm	25.40	BMP51, 53
Clear/White	38.10	152.40 mm	38.10	XSL-34-427	M-34-427	38.10	152.40 mm	38.10	BMP51, 53
Clear/White	44.45	25.40 mm	7.29	XSL-133-427	M-133-427	44.45	25.40 mm	7.29	BMP51, 53
Clear/White	44.45	38.10 mm	10.49	XSL-134-427	M-134-427	44.45	38.10 mm	10.49	BMP51, 53
Clear/Yellow	25.40	38.10 mm	12.70	XSL-31-427-YL-BK	M-91-427-YL	12.70	38.10 mm	12.70	BMP41, 51, 53
Clear/Yellow	25.40	63.50 mm	19.05	XSL-21-427-YL-BK	M-51-427-YL	19.05	63.50 mm	19.05	BMP41, 51, 53
Clear/Yellow	25.40	101.60 mm	25.40	XSL-23-427-YL-BK	M-53-427-YL	25.40	101.60 mm	25.40	BMP41, 51, 53
<b>B-461 Self-Laminating Polyester</b>									
Clear/White	25.40	44.45 mm	25.40	XSL-125-461	M-125-461	44.45	25.40 mm	25.40	BMP51, 53
Clear/White	25.40	66.68 mm	25.40	XSL-75-461	M-75-461	66.68	25.40 mm	25.40	BMP51, 53
Clear/White	28.58	9.53 mm	19.05	XSL-123-461	M-123-461	28.58	9.53 mm	19.05	BMP51, 53
Clear/White	28.58	12.70 mm	19.05	XSL-122-461	M-122-461	28.58	12.70 mm	19.05	BMP51, 53
Clear/White	38.10	57.15 mm	28.58	XSL-129-461	M-129-461	57.15	38.10 mm	28.58	BMP51, 53
Clear/White	38.10	95.30 mm	28.58	XSL-119-461	M-119-461	95.30	38.10 mm	28.58	BMP51, 53
Clear/White	41.91	12.70 mm	19.05	XSL-124-461	M-124-461	41.91	12.70 mm	19.05	BMP51, 53
Clear/White	44.45	12.70 mm	19.05	XSL-72-461	M-72-461	44.45	12.70 mm	19.05	BMP41, 51, 53
Clear/White	45.72	15.24 mm	25.40	XSL-126-461	M-126-461	45.72	15.24 mm	25.40	BMP51, 53
Clear/White	55.88	12.70 mm	19.05	XSL-74-461	M-74-461	55.88	12.70 mm	19.05	BMP51, 53
Clear/White	66.68	15.24 mm	25.40	XSL-86-461	M-86-461	66.68	15.24 mm	25.40	BMP51, 53
White	9.53	9.14 m	-	XC-375-461	MC-375-461	9.53	7.62 m	-	BMP51, 53
White	12.70	9.14 m	-	XC-500-461	MC-500-461	12.70	7.62 m	-	BMP41, 51, 53
White	25.40	9.14 m	-	XC-1000-461	MC-1000-461	25.40	7.62 m	-	BMP51, 53
White	31.75	9.14 m	-	XC-1250-461	MC-1250-461	31.75	7.62 m	-	BMP51, 53