


DATA SHEET IL-640 NIMH HAND LAMP

MODEL	IL-640 NiMH		
Product description	Rechargeable hand lamp		
Operating temperature	-20°C +40°C		
Light source	4 high luminous Cree LED's, lifetime: L70 >50 000 h		
Light output	High power Low power		
	600 lumen 160 lumen		
Operating time	Full power Low power		
	8 hours 24 hours		
Beam type	Spot		
Lens	Tempered glass 108 mm x 5 mm		
Enclosure	High impact polyamide		
Ingress protection	IP 67		
Colour	Yellow body / Black locking ring		
Power source	6V rechargeable NiMH battery		
Weight with battery	1,4 kg		
Dimensions	Approx. 215 mm (L) x 120 mm (W) x 125 mm (H)		
Charging time	11 h		
Other features			
	Deep discharge prevention		
	Low battery warning		
	Short circuit protection		
	Shoulder strap		
Chargers	MICA ILC4-VAC Single mains charger (85264VAC)		
	MICA ILC4 Single vehicle charger (1224VDC)		
	MICA CR-C3 Multi charger for 3 lamps (100240VAC)		
	MICA CR-C5 Multi charger for 5 lamps (100240VAC)		
Accessories	Colour filters: red, green and amber		
	Diffuser filter		
	Adjustable stand for a single lamp		





	1		1
Light output, Full power	L	W	Н
15lx limit	50m	3m	3m
0,5lx limit	265m	10m	10m
Light output, Low power	L	W	Н
15lx limit	23m	1,5m	1,5m
0,5lx limit	130m	6m	6m



Made in Finland by ATEXOR Oy

Tel: +358 207 343250, E-mail: info@atexor.com www.atexor.com

ATEXOR Oy prepared this information herein in good faith but makes no representation as to its comprehensiveness or accuracy. ATEXOR Oy reserves the right to make changes to specifications and product descriptions at any time without notice. Ask for more technical data from our sales support.