



### ANSMANN Work Light IL300R

- Professional work light with latest SMD LED technology
- Additional spotlight in lamp head
- Robust plastic housing with rubberized surface
- 180° rotatable lamp handle, (in 8 steps), for flexible lighting alignment
- Two foldable and 360° rotatable hooks at the back
- Two magnets at the back of the housing and one magnet at the bottom of the handle
- Impact protected Li-Ion battery pack (3.7V / 2200mAh)
- Charging via USB power supply (5V / 1000mA) or car adapter (12-24V) supplied
- Charge control indication via duo LED
- Illumination 555 Lux / 1m
- Luminous flux 325 Lumens (main light) / 110 Lumens (additional spotlight)
- Lighting duration approx. 3,5 hours / 9 hours
- Charging time: approx. 3 hours
- 2 years ANSMANN Germany warranty

### INFORMATION

<b>Product name:</b>	IL300R
<b>Article number:</b>	1600-0152
<b>EAN-Code:</b>	4013674106004
<b>Accessories incl.:</b>	USB power supply, USB car charger cable
<b>Product:</b>	274x64x40mm / 282g
<b>Packing + product:</b>	390x125x51mm / 459g