



Identification ties and plates for marking cable bundles

IT Ties

One of the major benefits is the ability to both secure and identify cable bundles at different times.

Features and benefits

- Identification ties made of Polyamide 6.6
- For simple identification and securing of cable bundles in one step
- Printable labels are available for a professional finish
- Manual or temporary marking is possible with an indelible pen (T82S-BK / T82R-RD)



One operation with two benefits.



MATERIAL	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C
Flammability	UL 94 V2



Please find the corresponding labels on page 497.

HF ✓

RoHS ✓



TYPE	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Length (L)	Width (W2)		Recommended Labels	Pack Cont.	Colour	Article-No.
IT18FL	1.5	19.0	20.5	9.0	110.0	2.5	80	TAG18-07TD1	100 pcs.	Natural (NA)	111-81919
	1.5	19.0	20.5	9.0	110.0	2.5	80	TAG18-07TD1	100 pcs.	Black (BK)	111-81910
IT18R	6.0	22.0	25.0	8.0	100.0	2.5	80	TAG23-06TD1	1,000 pcs.	Black (BK)	111-81860
	6.0	22.0	25.0	8.0	100.0	2.5	80	TAG23-06TD1	100 pcs.	Natural (NA)	111-81821

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.


 = Minimum Loop Tensile Strength for Cable Ties (newton)



For product specific approvals and specifications please refer to the Appendix.








Add items to your watchlist!
www.HT.click/49-495



Identification ties and plates for marking cable bundles

IT Ties



TYPE	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Length (L)	Width (W2)		Recommended Labels	Pack Cont.	Colour	Article-No.
IT50R	9.5	44.5	28.0	12.9	203.2	4.6	225	TAG23-10TD1	100 pcs.	Natural (NA)	111-85019
IT50RD	10.0	44.0	29.0	26.3	203.2	4.7	225	TAG26-21TD1	50 pcs.	Natural (NA)	111-85219
IT50RT	10.0	44.0	46.0	26.3	203.2	4.7	225	TAG43-21TD1	50 pcs.	Natural (NA)	111-85119
IT50L	19.0	100.0	56.0	12.8	390.0	4.7	225	TAG52-10TD1	100 pcs.	Natural (NA)	111-85319

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.

 = Minimum Loop Tensile Strength for Cable Ties (newton)

TYPE	Description	Pack Cont.	Colour	Article-No.
T82S-BK	Indelible Marker Pen	2 pcs.	Black (BK)	500-50820
T82R-RD	Indelible Marker Pen	2 pcs.	Red (RD)	500-50822

Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.

