

# KEL-ER 24 Cable Entry Frames



V2A anti-corrosive  
Also available with stainless steel screws (V2A).






Also available with threaded bushings.



Slit KT grommets



Type	Order No.	Grommets small   large	PU	Description
------	-----------	---------------------------	----	-------------

KEL-ER 24 10	48241	10 -	10	
KEL-ER 24 10 with V2A screws	48241.200	10 -	10	
KEL-ER 24 7	48247	6 1	10	
KEL-ER 24 7 with V2A screws	48247.200	6 1	10	
KEL-ER 24 4	48244	2 2	10	
KEL-ER 24 4 with V2A screws	48244.200	2 2	10	

## Product Description

Split cable entry system for routing and sealing cables with connectors, providing an IP65 / up to NEMA type 4X rating and strain relief for cable diameters from 1 to 16 mm (KT 1 - 15) and 16 to 35 mm (KT 16 - 34).

The new cable entry system is easy to install. Cable grommets are placed compartments in the frame and are securely fixed to the frame during assembly. The KEL-ER 24 frame matches exactly the cut-out dimensions for 24-pin standard industrial connectors. A flat rubber gasket is included in the shipment.

## Advantages & Benefits

- Warranty on pre-terminated cables remains
- Retrofits, repairs and maintenance can be done much more easily and quickly
- High cable density, wide variety of grommets
- Strain relief according to EN 62444
- High stability, vibration resistant

## Specifications

Material	Polyamide (PA)
Flame class	UL94-Vo
IP rating	IP65, with gasket and correct selection of single grommets (certified acc. to EN 60529)
NEMA type rating	NEMA type 4X (acc. to UL 50E)
Temperature	- 40°C to + 140°C (static) - 40°F to + 284°F (static)
Properties	Halogen-free, silicone-free
Cut-out dimensions	36/46 × 112 mm / Page 200 - 201
Frame depth	17 mm

## Accessories

KT Cable grommets	44 - 46
KEL-EMC Grounding mounts	126 - 128
ST Plugs	49