



ICY BOX IB-HUB1409-U3

4 port USB 3.0 hub

Key features

- 4 port USB 3.0 Hub
- Interface to PC: USB 3.0 Type-A up to 5 Gbit/s
- LED indicator
- Aluminum case
- Supports Windows, Linux, macOS 9 or later version



Packing content

1x IB-HUB1409-U3, 1x manual

Fit for the future!

With this hub you can use the fast USB 3.0 for four devices. The hub is buspowered so it is usable without power supply and the ideal extension on the move. USB 3.0 has a bandwidth of up to 5 Gbit/s. That makes it up to 10 times faster than USB 2.0. USB 3.0 is downwards compatible, it fits also USB 2.0 cables and devices (with lower transfer rates).

Technical data

Model	IB-HUB1409-U3
Article no.	60255
EAN code	4250078165873
Brand	ICY BOX
Article text	4 port USB 3.0 Hub
Color	Black
Material	Aluminum
Interface to PC	1x USB 3.0 Type-A

Interface	4x USB 3.0 Type-A up to 5 Gbit/s
HotSwap	Yes
Plug & Play	Yes
Chipset	VL812
Length of cable	40 cm
Operating system	Supports Windows, Linux, macOS 9 or later version
Power connector	USB powered
Operation temperature	0° - 60° C



ICY BOX **IB-HUB1409-U3** 4 port USB 3.0 hub



No more slots?

If you want to use your existing USB 3.0 devices on the latest mobile devices and laptops with a USB port this compact hub is a quick help. It uses a single USB 3.0 port on its own and creates four additional Type-A ports. Problem solved!



Well-known and still new

Like all our hubs the IB-HUB1409-U3 has the Plug & Play and HotSwap ability. These enable the driver-free installation of the device and the rapid replacement of the devices during operation. USB 3.0 has a transfer rate of up 5 Gbit/s.



Simple and chic

The IB-HUB1409-U3 is made from aluminium and thus very light even if you are on the move. The look, however, does not lose in importance, the hub presents itself with a sand blasted surface.

Logistical data

Packing unit:	60 pcs./carton
Total weight:	9.6 kg/carton
Gross weight: (with packing):	0.143 kg
Net weight:	0.068 kg

Dimension/carton:	428x428x270 mm
Dimension (with packing):	26x101x203 mm
Dimension of article:	21x29x95 mm
Country of origin:	China

