



ICY BOX IB-HUB1426-U3

USB 3.0 HUB Type-A to 2x Type-CTM and 2x Type-A ports

Key features

- USB Type-A hub with 2x Type-C[™] and 2x Type-A USB ports
- 2x USB Type-C™ with a transfer rate up to 5 Gbit/s
- 2x USB Type-A with a transfer rate up to 5 Gbit/s
- Housing made of high-grade aluminium and plastic
- Supports Windows®, macOS®
- Integrated USB cable 10 cm length



Packing content

1x IB-HUB1426-U3, 1x quick installation guide

Small and handy

Due to its handy size the IB-HUB 1426-U3 fits into every pocket without any problems and brings along USB 3.0 as well as the USB Type-A and the USB Type-C™ connection standards.

Technical data

 Model
 IB-HUB1426-U3

 Article no.
 60493

 EAN code
 4250078168799

 Brand
 ICY BOX

 Colour
 Black

2x USB 3.0 Type-C⁻⁻ 2x USB 3.0 Type-A **Transfer rate** Up to 5 Gbit/s

UASP support Yes Plug & Play Yes

Power supply Bus powered - optional 5 V power supply can be

connected, connector size 3.5x1.35x10 mm (not

Operating system included)

Windows®, macOS®







ICY BOX **IB-HUB1426-U3** USB 3.0 HUB Type-A to 2x Type-CTM and 2x Type-A ports



Noble design

IB-HUB 1426-U3 offers not only functionality but also a stylish design. The high-quality aluminium housing lets other enclosures stand in the dark and the rounded edges along with the smooth side make the HUB a real eye-catcher.



50-50

The middle does the trick - and IB-HUB1426-U3 demonstrates it. It has two USB Type-C™ as well as two Type-A connectors and keeps the balance between the longstanding connections and those that are entering the work and living rooms. This makes it the perfect companion for existing equipment as well as for equipment purchased in the future.



10 cm integrated cable

By using the integrated cable you'll never ask yourself, Where did I leave the fitting cable? because now you are always ready to plug in the device.

Logistical data

 Packing unit:
 60 pcs./carton

 Total weight:
 8.8 kg/carton

 Gross weight: (with packing):
 0.135 kg

 Net weight:
 0.070 kg

 Dimension/carton:
 448x271x322 mm

 Dimension (with packing):
 25x100x200 mm

 Dimension of article:
 90x40x15 mm

 Country of origin:
 China

RaidSonic Technology GmbH