


 ZENIT EVO 7148

EN ISO 20345:2011 S3, SRC



Learn more

A LIGHTER SHOE FOR THOSE ON THE GO

A lightweight safety shoe with knitted textile upper and laces. Outstanding ergonomics, padded Memory foam and water repellency means day-long safety and comfort. An oil resistant RPU outer sole gives outstanding grip and a ventilated inner sole keeps feet cool. Features JALAS® aluminium toe cap, plasma-treated textile puncture protection and double impact protection zones in PORON® XRD®.

CHARACTERISTICS

- Excellent shock absorption
- Excellent grip
- Perfect fit
- Extra comfortable
- Very breathable
- Extremely light

FUNCTIONS

- Oil-resistant outsole
- Anti-static properties
- Water repellent
- Ergonomically shaped
- Ventilating insole
- Low weight
- Bellows tongue
- Conforms with IEC 61340-5-1 (ESD)
- Padded shaft edge in memory foam
- Free from animal-derived materials



PREVENTS RISK OF

Toe injuries, nail penetration, antistatic, slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, indoors, environments with risk for outsole penetration, dry environments, clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes

CATEGORY Cat. II

NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile

FITTING Regular

COLLECTION Zenit Evo

UPPER MATERIAL Knitted textile

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester

INSOLE FX3 Supreme

INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, Double shock absorption zones in Poron® XRD®

MIDSOLE MATERIAL PU midsole

OUTSOLE MATERIAL RPU outsole

FASTENING Laces

COLOUR Black

NET WEIGHT, (SIZE 42) 1.17 kg

COMPLIANCE



TP TC 019:2011

EN ISO 20345:2011 S3, SRC



ÖNORM Z 1259



DGVV 112-191

FEATURES



Anti-static properties



Ergo-Shock Absorption System



ESD



Aluminium toecap



Oil-resistant outsole



Water repellent



Nail protection in plasma-treated composite (PTC) textile

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3½	4	7148-35	6408487508332
36	3	4	5	7148-36	6408487508349
37	4	5	6	7148-37	6408487508356
38	5	5½	6½	7148-38	6408487508363
39	6	6½	7½	7148-39	6408487508370
40	6½	7½	8½	7148-40	6408487508387
41	7	8	9	7148-41	6408487508394
42	8	9	10	7148-42	6408487508400
43	9	9½	11	7148-43	6408487508417
44	10	10½	11½	7148-44	6408487508424
45	10½	11	12½	7148-45	6408487508431
46	11	12	13	7148-46	6408487508448
47	12	13	14	7148-47	6408487508455
48	13	13½	14½	7148-48	6408487508462

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com