



# JAYBIRD X4

Wireless Sports Headphones



## RUGGED VERSATILITY FOR THE ALL-AROUND RUNNER AND OUTDOOR ATHLETE

At our core we are runners, but the life of an outdoor athlete thrives with balance. From trail runs and mountain bike rides to summit scrambles and deep powder days, our passion for the outdoors is a thread that runs through a variety of pursuits. The X4 embodies that spirit of versatility. The evolution of our do-it-all wireless headphones for the all-around runner and outdoor athlete—comfortable, rugged and fully waterproof to tackle any run, ride or trail in any conditions.

### FEATURES

- 8 hrs of wireless play time on a single charge
- Sweat and waterproof for any weather conditions
- Sport Fit Plus design for a secure fit
- Comply Ultra™ Foam Tips for a customizable fit
- Premium sound with custom EQ via app
- Control music and calls with the push of a button

### WHAT'S IN THE BOX

- Jaybird X4 Sport Wireless Headphones
- Comply Ultra Ear Tips M/L
- Oval Silicone Ear Tips S/L
- Secure-Fit Ear Fins 1/2/3
- Speed Cinch
- USB 2.0 Charging Cable
- Shirt Clip
- Carry Pouch

### SYSTEM REQUIREMENTS

- *Bluetooth®* compatible device



## PACKAGE SPECIFICATIONS

	Single	Case Pack
Part # Storm Metallic/Glacier	985-000809	N/A
UPC Storm Metallic/Glacier	097855143211	10097855143218
Part # Black Metallic/Flash	985-000808	N/A
UPC Black Metallic/Flash	097855143204	10097855143201
Weight	6.70 oz.	35.27 oz.
Width	2.09 in.	5.39 in.
Length	4.96 in.	9.02 in.
Height	7.20 in.	7.87 in.
Case Pack Count	N/A	4 single units
Pallet Count	720 units	180 case packs



## TECHNICAL SPECS

### AUDIO

- Type: In-Ear Style
- Noise-isolation: Passive
- Impedance: 16 Ohm
- Speaker sensitivity: 99 +/-3dB At 1KHz
- Output max. 10mW RMS (with level limit)
- Total Harmonic Distortion <5% (1KHz, 1mW)
- Audio Format: 16-bit Stereo
- Codec: Bluetooth SBC Implementation
- Response Bandwidth 20Hz - 20kHz
- Driver Size: 6 mm

### BLUETOOTH®

- *Bluetooth* Version: 4.1
- Frequency Band: 2.4 GHz
- Profiles: Handsfree, Headset, A2DP, AVCRP, SPP
- Wireless Range: Class 2 standard range 10m/33ft

### INTEGRATED MICROPHONE

- Type: MEMS, Omni directional
- Sensitivity: -38dB +/-3dB (Test conditions:94dB SPL, 1KHz, A-Weighted)

### BATTERY

- Play Time: 8+ Hrs\*
- Charging Time: 2 Hrs

### WEIGHT & DIMENSIONS

- Headset: 501mm x 13mm x 23.6mm
- Controller: 42.4mm x11.6mm x 6.35mm
- Charger: 95mm x 18.1mm x 9.4mm
- Weight of single bud (no Fins and Tips): 14.8g
- Weight of Charger: 5.9g