
KEMET Part Number: C878AF35315AA0J



C87, Film, Film/Foil Polypropylene, Motor Run, 31.5 uF, 5%, 470 VAC



Dimensions		
D	45mm +1mm	
L	98mm +/-2mm	

Packaging Specifications		
Mounting:	Bolt - M8x10	
Packaging:	Bulk, Bag	
Packaging Quantity:	50	

General Information		
Supplier:	KEMET	
Series:	C87	
Dielectric:	Film/Foil Polypropylene	
Style:	Can	
Description:	Aluminum Case, Plastic Cover, Spun Seal	
Features:	Spun Seal, Safety Class S2, UL_94 V0 Disk	
RoHS:	Yes	
Lead:	Fast On (2+2)	
Qualifications:	UL, VDE, CQC, CSA (240VAC), UL_94 V0 Disk	

Specifications		
Capacitance:	31.5 uF	
Capacitance Tolerance:	5%	
Voltage AC:	470 VAC	
Temperature Range:	-25/+85C	
Rated Temperature:	85°C	
Max dV/dt:	20 V/us	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

