

CATV Amplifier 18 dB 40-862 MHz 2 Outputs

General information

Amplifier with gain control and two outputs to connect to a home installation and receive ultra-clear TV signals.

Features

- Plug & play
- IEC connector for quick installation

Specifications

Output level:	100 dBuV
Power consumption in operating mode:	250 mA
Frequency range:	40-862 MHz
Impedance:	75 Ohm
Gain:	18 dB
Noise figure:	6 dB
No. of inputs:	1
No. of outputs:	2
Colour:	White
Usage:	Indoor
Power plug:	Euro / Type C (CEE 7/16)
Application:	CATV
Input voltage:	12 V
Connector type:	IEC Connector

Package contents

1 x antenna amplifier
1 x power adapter
1 x installation material manual



Sales information

Order code: **KN-AMP20**
Product description: CATV Amplifier 18 dB 40-862 MHz 2 Outputs
Packaging: Giftbox with eurolock
Brand name: König



5 41 281 0 | 2161 09

Quantity	LxWxH (mm)	Weight
1	105x70x265	273 gr.
20	355x230x480	5960 gr.